

**H.K. Porter**  
**42" Industrial Grade, Center Cut Cutter**



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	0590MC
UPC Code	037103910790
Weight/Length	17 1/8 lbs./42 in.
Handle Material	Tubular Steel
Jaw Design/Cutting Blade	All Purpose/Center Cut
Replacement Cutterhead/Jaws	0513C
Capacity	See Tech Specs Link Below
Material Hardness	See Tech Specs Link Below
Brinell/Rockwell	See Tech Specs Link Below
Packaging	Industrial Box/Carton
Literature	<a href="#">Safety- Hand Tool Selection.pdf</a>
Tech. Spec.	<a href="#">0590MC Specifications.pdf</a>
Lineart	<a href="#">0090MC.pdf</a>
Low Res. Image	<a href="#">0590MC_100.jpg</a>
High Res. Image	<a href="#">0590MC_300.jpg</a>
Parts List	<a href="#">Parts for 0590MC.pdf</a>
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

**Product Features:**

- General plant maintenance tool
- Drop-forged, precision ground, alloy tool steel jaws, center-cut blades
- Cuts soft, medium, or hard materials
- Maximum hardness of material to be cut: Brinell 455/Rockwell C48
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lb hand pressure to 4000 lb cutting pressure

- **Screw-type adjustment realigns edges**
- **Steel handles with rubber grips**
- **Replacement cutterhead" 0513C**
- **NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!**