Tweezers

Precision tweezers: Pointed tips straight

120 mm/4.724 Inch

	Model	T	Description
	00SASL*	20 g 0.71 oz.	Same as OOSA, but economy model.
an Q	00CSA	18 g 0.64 oz.	Model same as 00SA, but with shorter tips.
	00BSA	20 g 0.71 oz.	Model same as 00SA, but with serrated finger grips for secure handling.
	00DSA	20 g 0.71 oz.	Model same as 00SA, but with serrated finger grips and inside-serrated tips for secure handling.
11-12	64SA	17 g 0.60 oz.	Precision tweezers with pointed tips and serrated finger grips for secure handling.
	11N	17 g 0.60 oz.	Precision tweezers with medium-pointed tips for use on soft components. Nickel-silver , non-magnetic.
2	AAZ*	16 g 0.56 oz.	Precision tweezers with medium-pointed tips, nickel-plated . Suitable for electronic assembly tasks.

125 mm/4.921 Inch



Model	- -	Description
AAS	16 g	Precision tweezers with fine but robust tips.
AASA	16 g	Precision tweezers with fine but robust tips for standard applications.
AASASL*	16 g	Same as AASA, but economy model.

*Not available in North America