Powerful capability

Another Weller breakthrough-Powerful 80-watt performance combined with a new shorter handle

WP80

Two Pencils In One

This powerful 80-watt pencil allows rapid production when working with lead-free solder, high-mass components, and other demanding applications. A special silver heating element for low thermal loss and fast recovery make this unit ideal for continuous production work.

Specifications:

WP80 Pencil Power Consumption Voltage Heating Element Type Cord Length Supplied Tip

80W 24 V Nichrome Wound Silver Spool 4 ft. (1.22 m)



The Silver Spool heating element provides low thermal loss and fast recovery

> Optional longer barrel available

WMP

The accuracy and economy champ

With a tip-to-grip distance of just 37 mm, accuracy is unsurpassed. And the WMP heating element is built into the pencil, not the tip, so replacement tips cost substantially less. This pencil offers super fast heat-up and superior thermal recovery for fast, efficient soldering.

Specifications:

WMP Pencil

Power Consumption 65 W Voltage

Heating Element Type

Cord Lenath Supplied Tip 24 V

NT1

Nichrome Wound Silver Spool 4 ft. (1.22 m)

