



















Hot air nozzles for HAP1 WRS3000S, WRS1002, WAD101

	Model	Dimensions	Components	Description	Order No.
Round nozzles					
	F06	12,0 x 1,5 mm		flat nozzle	0058727772
	F04	10,5 x 1,5 mm		flat nozzle	0058727773
	F02	8,0 x 1,5 mm		flat nozzle	0058727774
	R10	Δ 2,0 mm		round nozzle	0058727787
	R08	Δ 2,0 mm		round nozzle, bent	0058727786
	R06	Δ 3,0 mm		round nozzle	0058727822
	R04	Δ 1,2 mm		round nozzle	0058727821
	R02	Δ 0,8 mm		round nozzle	0058727823
	FD4	Δ 1,5 x 10,0 mm		dual nozzle	0058727775
	FD2	Δ 1,5 x 8,0 mm		dual nozzle	0058727776



Model	Dimensions X x Y	Components	Description	Order No.	
Two sides heated (type D)					
	D10	18,0 x 10,0 mm	SO 28	hot air nozzle with hotplate	0058727784
	D08	15,0 x 10,0 mm		hot air nozzle with hotplate	0058727781
	D06	13,0 x 10,0 mm		hot air nozzle with hotplate	0058727782
	D04	10,5 x 10,5 mm		hot air nozzle with hotplate	0058727779
All 4 sides heated (type D)					
	Q08	12,5 x 15,0 mm		hot air nozzle with hotplate	0058727783
	Q06	15,0 x 10,0 mm		hot air nozzle	0058727780
	Q04	6,0 x 9,0 mm		hot air nozzle	0058727778
	Q02	6,0 x 6,5 mm		hot air nozzle	0058727777