

H.K. Porter

42" Shear Type Cable Cutter for Wire Rope up to 3/4"



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	0590MTN
UPC Code	037103910875
Weight/Length	17 lbs./42 in.
Handle Material	Tubular Steel
Jaw Design/Cutting Blade	Blade/Shear Cut
Replacement Cutterhead/Jaws	0513TN
Capacity	See Tech Specs Link Below
Material Type	See Tech Specs Link Below
MCM/Inches	See Tech Specs Link Below
Packaging	Industrial Box/Carton
Literature	Safety- Hand Tool Selection.pdf
Tech. Spec.	0590MTN Specifications.pdf
Lineart	1490MTN.pdf
Low Res. Image	0590MTN_100.jpg
High Res. Image	0590MTN_300.jpg
Parts List	Parts for 0590MTN.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Notched, shear-cut blades hold and lock cable in cutting position
- Cuts steel cable, coarse- or fine-stranded cable with minimal distortion
- Cuts wire rope with minimal distortion
- Toggle joints turn 50 lb hand pressure to 4000 lb cutting pressure
- Screw-type adjustment realigns edges
- Replacement cutterhead: 0513TN
- NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!

