

Xcelite  
ErgoCrimp Plus® for 22-10 AWG Non-insulated Terminals Splices

◀◀ previous print close next ▶▶

Product Details

|                            |  |
|----------------------------|--|
| Catalog No.                | ECP101                                       |
| UPC Code                   | 037103197146                                 |
| Crimping Range             | 22-10 AWG                                    |
| Connector Type             | Non-insulated<br>Terminal/Splices            |
| Wire or Cable<br>Size/Type | Solid/Stranded                               |
| Die Set                    | D101   |
| Packaging                  | Industrial Box/Carton                        |
| Tech. Spec.                | <a href="#">Crimping Stripping Tools.pdf</a> |
| Operating Ins.             | <a href="#">Crimp Tools Instructions.pdf</a> |
| Stock Item                 | Normal Stock Item                            |

Package Details (Dimensions)

Email this Page

Product Features:

- Die set designed for 22-10 AWG non-insulated terminal splices
- Patented ergonomic design makes this tool easy and comfortable to use
- Lowest possible handle forces required
- High quality construction with tight tolerances
- Superior crimp die design insures the highest quality crimp results
- High strength through-hardened alloy steel and precision manufacturing
- Guaranteed for 50,000 cycles
- Precise eccentric adjustment for consistent performance for life of tool
- Tools can be purchased complete with die set or separately
- Special dies are also available upon request