Benchtop Shot Meter with Vacuum Only



44 previous	print	close	next 🕨	
Product Details				
Catalog No.	-	KDS808		
UPC Code		037103173706		
Input voltage		115 V 230 V		
Output Voltage	ut Voltage		24 V	
Air Input/Output	:	0-100 psi		
Vacuum		0-18 in. Hg		
Timer Ranger		No Timer		
Packaging		Industrial Box/Carton		
Literature		5506901A.pdf		
Low Res. Image		KDS8	08_100.jpg	
High Res. Image		KDS8	<u>08_300.jpg</u>	
Operating Ins.	<u>KDS</u>	808_834	A_824A_OI_PL.pdf	
Parts List	<u>KDS</u>	808_834	A_824A_OI_PL.pdf	
Stock Item		Normal Stock Item		

Package Details (Dimensions)

Email this Page

Product Features:

- Basic low cost system
- Easy to set up and operate, "Eyeball†accuracy
- Electrically actuated foot pedal
- Vacuum feature prevents dripping
- 0 100 PSI regulators and gauges with locking ring
- Benchtop unit; easy reading of dials, adjustment of air pressure, vacuum
- Low voltage unit, slide switch easily changes unit from 115 to 230 volts
- Order syringe adapters, kits and other accessories separately