

# Die Set, Non-Insulated Terminals, for Crimpmaster™ Crimp Tool Frame 30-506

Catalog # 30-580



### **Features**


- For non-insulated terminals #8 to #22 AWG (.3mm2 to 8mm2)
- · Provides good and consistent crimp every time
- Dies change quickly and easily with a screwdriver
- Interchangeable dies provide versatility in a single tool

## **DataComm Equipment**

#### **Crimpmaster<sup>™</sup> Crimp Tools & Die Sets**

High quality ratchet-type crimp tool for electricians, contractors and installers who require guaranteed repeatability of good mechanical and electrical connections.

Description



### Also available in these kits:

30-587

30-591

(1.73mm), 0.042 (1.07mm) Tool w/die N/A

Plenum and Non-Plenum Thinwire

Cables RG-58 and 59 (Hex, 0.213

(5.41mm), 0.190 (4.83mm), 0.068

(1.73mm), 0.042 (1.07mm)



Crimpmaster™ Crimp Tool Frame

33-917





Cat. No.

30-506









G-11

30-479 (Tool w/die) For insulated terminals, 22-10 AWG with built-in locator

















Tool w/die N/A

### 30-594

Fully Insulated quick disconnect terminals with thinner wire barrels 22-10 AWG (.324mm<sup>2</sup> - 5.261mm<sup>2</sup>) Tool w/die N/A

30-599 30-18 AWG (.205mm<sup>2</sup> - 2.08mm<sup>2</sup>) Open Barrel Pins and Sockets Tool w/die N/A



## 30-573

and butt splices Tool w/die N/A

pluas

Cambridge CP-88, CP-89 BNC/TNC coax connectors with RG-58, RG-59/RG-62 AU cables (Hex 0.305 (7.75mm), 0.068 (1.73mm), 0.228 (5.79mm)

#### Tool w/die 30-481

30-576

RG-174, Mini 59 BNC/TNC Connectors (Hex, 0.178 (4.52mm), 0.128 (3.25mm), 0.068 (1.73mm) Tool w/die 30-485

Connectors (Hex, 0.255 (6.48mm),

0.213 (5.41mm), 0.068 (1.73mm) Tool w/die 30-502 30-582



F-type CATV RG-59, RG-6 Connectors (Hex, 0.350 (8.89mm), 0.320 (8.13mm), 0.255 6.48mm) Tool w/die 30-503

#### 30-586 22-12 AWG (.324mm<sup>2</sup> - 3.31mm<sup>2</sup>) Non Insulated Open Barrel Connectors, Commercial Type Tool w/die N/A









