

Crimpmaster[™] Crimp Tool, for CATV RG-59 and RG-6 Captive Ring F-Connectors

Catalog # 30-503



Features

- · Provides good and consistent crimp every time
- · Dies change quickly and easily with a screwdriver
- Interchangeable dies provide versatility in a single tool
- Cushioned, comfort-grip handles

DataComm Equipment

Crimpmaster™ Crimp Tools & Die Sets

High quality ratchet-type crimp tool for electricians, contractors and installers who require guaranteed repeatability of good mechanical and electrical connections.



Description	Cat. No.
Crimpmaster™ Crimp Tool Frame	30-506

Also available in these kits:

33-400





30-556

RJ-11 Crimp Tool for two, four or six-position modular plugs Tool w/die N/A



N-Series and RG-8/11 Connectors (Hex, 0.429 (10.90mm), 0.100 (2.54mm), 0.080 (2.03mm) Tool w/die 30-482



RG-58, RG-174 and RG-8218 for both 50 and 75 ohm cables (Hex 0.213 (5.41mm), 0.178 (4.52mm), 0.068 (1.73mm), 0.042 (1.07mm) Tool w/die N/A



30-559

RJ-45 Eight-position Crimp Tool for keyed or non-keyed modular

Tool w/die 30-522



30-578

RG-59, RG-6, and 8281 50 and 75 OHM cables (Hex, 0.324(8.23mm), 0.255 (6.48mm), 0.068 (1.73mm), 0.042 (1.07mm)

Tool w/die 30-483



30-591

Plenum and Non-Plenum Thinwire Cables RG-58 and 59 (Hex, 0.213 (5.41mm), 0.190 (4.83mm), 0.068 (1.73mm), 0.042 (1.07mm) Tool w/die N/A



30-560

RJ-45 Eight-position Crimp Tool for AMP RJ-45 modular plugs Tool w/die 30-521



22-10 AWG (.324mm² - 5.261mm²) insulated terminals/color coded nests

Tool w/die 30-500



Mini UHF and BNC/TNC 5 cavity (Hex, 0.052 (1.32mm), 0.068 (1.73mm) 0.100 (2.54mm), 0.213 (5.41mm), 0.255 (6.48mm)

Tool w/die N/A



30-570

RG-6, RG-174, Belden-Type RG-8281 cables (Hex. 0.324 (8.23mm), 0.178 (4.52mm), 0.068 (1.73mm)

Tool w/die N/A



30-580

22-8 AWG (.3mm² - 8mm²) non-insulated terminals Tool w/die N/A



30-594

Fully Insulated quick disconnect terminals with thinner wire barrels 22-10 AWG (.324mm² - 5.261mm²) Tool w/die N/A



30-572

16-26 AWG (1.31mm² - .128mm²) miniature insulated rings, spade and butt splices

Tool w/die N/A



30-581

RG-58, RG-59/62, BNC/TNC Coax Connectors (Hex, 0.255 (6.48mm), 0.213 (5.41mm), 0.068 (1.73mm) Tool w/die 30-502



30-599

30-18 AWG (.205mm² - 2.08mm²) Open Barrel Pins and Sockets Tool w/die N/A



30-573

Cambridge CP-88, CP-89 BNC/TNC coax connectors with RG-58, RG-59/RG-62 AU cables (Hex 0.305 (7.75mm), 0.068 (1.73mm), 0.228 (5.79mm)



RG-174, Mini 59 BNC/TNC Connectors (Hex. 0.178 (4.52mm), 0.128 (3.25mm), 0.068 (1.73mm)

Tool w/die 30-485



30-582

F-type CATV RG-59, RG-6 Connectors (Hex, 0.350 (8.89mm), 0.320 (8.13mm), 0.255 6.48mm) Tool w/die 30-503



30-479 (Tool w/die)

For insulated terminals, 22-10 AWG with built-in locator



22-12 AWG (.324mm² - 3.31mm²) Non Insulated Open Barrel Connectors, Commercial Type Tool w/die N/A



