





In-Sure™ Push-In, 5-Port



| <u>Models</u> | <u>Models</u> | <u>Wire Sizes</u> | | | |
|---|---------------|-------------------|-----------|-------------|----------------|
| | Model | Color | Ports | Quantity | Catalog Number |
|  | 32 | Red | 2 | Box of 100 | 30-1032 |
| | | | | Jar of 300 | 30-1032J |
| | | | | Box of 5000 | 30-1632 |
|  | 33 | Orange | 3 | Box of 100 | 30-1033 |
| | | | | Jar of 250 | 30-1033J |
| | | | | Box of 5000 | 30-1633 |
|  | 34 | Yellow | 4 | Box of 100 | 30-1034 |
| | | | | Jar of 200 | 30-1034J |
| | | | | Box of 5000 | 30-1634 |
|  | 39 | Blue | 3 | Box of 50 | 30-1039 |
| | | | | Jar of 150 | 30-1039J |
| | | | | Box of 5000 | 30-1639 |
|  | 87 | Gray | 5 | Jar of 150 | 30-087J |
| | | | | Box of 1000 | 30-187 |
| | | | | Box of 5000 | 30-687 |
| | 88 | Blue | 6 stacked | Jar of 100 | 30-088J |
| | | | | Box of 1000 | 30-188 |

In-Sure™ Push-In, 5-Port

| | | | | | |
|---|----|-------|---|-------------|---------|
|  | | | | Box of 5000 | 30-688 |
|  | 90 | Black | 8 | Jar of 100 | 30-090J |
| | | | | Box of 1000 | 30-190 |
| | | | | Box of 5000 | 30-690 |

©2012 IDEAL INDUSTRIES, INC. All rights reserved.



In-Sure™ Push-In, 5-Port



| <u>Models</u> | <u>Models</u> | <u>Wire Sizes</u> | |
|---------------|-------------------|---|---|
| Models | Solid | Stranded | Stranded (Tin Bonded) |
| 32, 33, 34 | #12 AWG - #20 AWG | #12 AWG - #16 AWG (19 strand or less) #18 AWG (7 strand) | #14 AWG - #18 AWG (19 strand or less) |
| 39 | #10 AWG - #14 AWG | #10 AWG - #12 AWG (19 strand or less) | #10 AWG - #14 AWG (19 strand or less) |
| 87, 88, 90 | #12 AWG - #20 AWG | #14 AWG - #16 AWG (19 strand or less) #18 AWG (7 strand or less) | #12 AWG - #14 AWG (19 strand or less) #16 AWG (26 strand or less) 318 AWG (16 strand or less) |

©2012 IDEAL INDUSTRIES, INC. All rights reserved.