




## WeatherProof® MODEL 62® CONNECTOR, Card of 20



### Product Resources

[WeatherProof™ and UnderGround™ Wire Connectors Brochure](#)  
(PDF | 1782K)

[WeatherProof™ Wire Connectors MSDS](#)  
(PDF | 198K)

[IDEAL Connector UL Listed Wire Combinations](#)  
(PDF | 378K)

### Features

- UL listed to 486D for use in damp/wet locations
- Handles wire sizes from #18 to #8 AWG copper
- Minimum of 2 #18 AWG
- Maximum of 3 #10 AWG
- Swept-wing design for comfort and greater leverage
- Hexagonal shape allows connectors to be applied with standard nutdriver
- Card of 20
- Silicone-based sealant protects against moisture and corrosion
- Easy to apply pre-filled twist-on wire connectors
- Live-action, square-wire spring
- No pre-twisting required
- Shell rated for 105° C

### Models

Description	Catalog #
WeatherProof® MODEL 62® CONNECTOR, Card of 20	30-1162

©2014 IDEAL INDUSTRIES, INC. All rights reserved.