

Safe-T-Grip Fuse Puller

Catalog # 34-001



Features

- Small Puller for 250V, 9/32 inch to 1/2 inch diameter fuses
- 5 inches long
- Handy and convenient for removing or replacing cartridge-type fuses
- Three sizes handle fuses ranging from 0 to 600A
- Fully insulated, high dielectric, glass filled polypropylene construction
- Notched handles provide safe, no-slip grip
- Clearly marked amperage ranges

Fuse Puller and Test Light

- Convenient pocket-sized tool safely pulls cartridge fuses and checks electrical connections
- Test prods fit parallel and tandem slot receptacles
- Built-in resistors limit current flow to eliminate false indication
- For 9/16 in. to 1 in. fuses
- For use on fuses to 100A/250V and 60A/600V
- Test capacity from 100V to 600V AC/DC

| Description | Cat. No. |
|-------------------------------|----------|
| Fuse Puller & Test Light only | 34-012 |

Safe-T-Grip® Fuse Pullers

- Maximum efficiency and convenience for removing or replacing cartridge-type fuses
- Three sizes handle fuses ranging from 0 to 600A
- Fully insulated, high-dielectric, glass-filled polypropylene construction
- Notched handles provide safe, no-slip grip
- Clearly marked amperage ranges
- Exceed MIL specifications

| Description | Cat. No. |
|--|----------|
| Small Puller for 250V, 9/32 in. to 1/2 in. dia. fuses; 5 in. long | 34-001 |
| Medium Puller for 0 to 100A/250V & 600V, 1/2 in. to 1 in. dia. fuses; 7-1/2 in. long | 34-002 |
| Large Puller for 31 to 600A/250V & 31 to 400A/600V, 3/4 in. to 2-1/2 in. dia. fuses; 11-3/4 in. long | 34-003 |

Tuff-Grip™ Fish Tapes

- Large 16 in. case accommodates long tape lengths
- Large, comfortable, durable handle provides secure grip and ease of use
- Durable impact-resistant case



| Description | Cat. No. | Replacement Tape Cat. No. |
|--|----------|---------------------------------|
| S-Class® Fish Tape with Leader – 200 ft. | 31-064 | 31-155 |
| S-Class® Fish Tape with Eyelet – 200 ft. | 31-065 | 31-165 |
| Zoom™ – 200 ft. | 31-096 | 31-097 |

Fuse Pullers

- Molded of tough, high-impact nylon for greater strength
- No-slip gripping surface and protective finger stops for added safety



| Description | Cat. No. |
|---|----------|
| Small Puller for 0 to 30A/250V, 1/4 in. to 1/2 in. dia. fuses; 5 in. long | 34-015 |
| Large Puller for 0 to 100A/250V & 0 to 60A/600V, 9/16 in. to 1 in. dia. fuses; 7-1/4 in. long | 34-016 |



- 1000V AC, 1500V DC rated per ASTM F 1505-01 and EN 60900 (IEC900)
- Contains: 1/4 in. slotted, 3/16 in. slotted, #1 Phillips, #2 Phillips and 1/4 in. nutdriver
- Accommodates most standard 1/4 in. hex bits
- Powerful magnet securely holds bits in place
- Handle will store up to eight standard bits
- Strong 6 in. non-conductive composite material shank

| Description | Cat. No. |
|---|----------|
| 5-in-1 Non-Conductive Screwdriver/Nutdriver | 35-9905 |
| 1/4 in. Slotted Replacement Bit | LA-4125 |
| 3/16 in. Slotted Replacement Bit | LA-4126 |
| #1 Phillips Replacement Bit | LA-4127 |
| #2 Phillips Replacement Bit | LA-4128 |

1000V Insulated Screw-Holding Screwdriver

- Split blade wedges into screw slot when collar is extended
- Holds screw in place when installing in hard to reach areas
- Easy to start screw when wearing gloves

| Description | Cat. No. |
|---|----------|
| 1000V Insulated Screw Holding Screwdriver, 3/16 x 6 in. slotted Tip | 35-9406 |