

Safe-T-Grip Fuse Puller

Catalog # 34-002



Features

- Medium Puller for 0 to 100A/250V and 600V 1/2 inch to 1 inch diameter fuses
- 7-1/2 inches long
- Handy and convenient for removing or replacing cartridge-type fuses
- Three sizes handle fuses ranging from 0 to 600A
- Fully insulated, high dielectric, glass filled polypropylene construction
- Notched handles provide safe, no-slip grip
- Clearly marked amperage ranges

Fuse Puller and Test Light

- Convenient pocket-sized tool safely pulls cartridge fuses and checks electrical connections
- Test prods fit parallel and tandem slot receptacles
- Built-in resistors limit current flow to eliminate false indication
- For 9/16 in. to 1 in. fuses
- For use on fuses to 100A/250V and 60A/600V
- Test capacity from 100V to 600V AC/DC

Description	Cat. No.
Fuse Puller & Test Light only	34-012

Safe-T-Grip® Fuse Pullers

- Maximum efficiency and convenience for removing or replacing cartridge-type fuses
- Three sizes handle fuses ranging from 0 to 600A
- Fully insulated, high-dielectric, glass-filled polypropylene construction
- Notched handles provide safe, no-slip grip
- Clearly marked amperage ranges
- Exceed MIL specifications

Description	Cat. No.
Small Puller for 250V, 9/32 in. to 1/2 in. dia. fuses; 5 in. long	34-001
Medium Puller for 0 to 100A/250V & 600V, 1/2 in. to 1 in. dia. fuses; 7-1/2 in. long	34-002
Large Puller for 31 to 600A/250V & 31 to 400A/600V, 3/4 in. to 2-1/2 in. dia. fuses; 11-3/4 in. long	34-003

Tuff-Grip™ Fish Tapes

- Large 16 in. case accommodates long tape lengths
- Large, comfortable, durable handle provides secure grip and ease of use
- Durable impact-resistant case



Description	Cat. No.	Replacement Tape Cat. No.
S-Class® Fish Tape with Leader – 200 ft.	31-064	31-155
S-Class® Fish Tape with Eyelet – 200 ft.	31-065	31-165
Zoom™ – 200 ft.	31-096	31-097

Fuse Pullers

- Molded of tough, high-impact nylon for greater strength
- No-slip gripping surface and protective finger stops for added safety



Description	Cat. No.
Small Puller for 0 to 30A/250V, 1/4 in. to 1/2 in. dia. fuses; 5 in. long	34-015
Large Puller for 0 to 100A/250V & 0 to 60A/600V, 9/16 in. to 1 in. dia. fuses; 7-1/4 in. long	34-016



- 1000V AC, 1500V DC rated per ASTM F 1505-01 and EN 60900 (IEC900)
- Contains: 1/4 in. slotted, 3/16 in. slotted, #1 Phillips, #2 Phillips and 1/4 in. nutdriver
- Accommodates most standard 1/4 in. hex bits
- Powerful magnet securely holds bits in place
- Handle will store up to eight standard bits
- Strong 6 in. non-conductive composite material shank

Description	Cat. No.
5-in-1 Non-Conductive Screwdriver/Nutdriver	35-9905
1/4 in. Slotted Replacement Bit	LA-4125
3/16 in. Slotted Replacement Bit	LA-4126
#1 Phillips Replacement Bit	LA-4127
#2 Phillips Replacement Bit	LA-4128

1000V Insulated Screw-Holding Screwdriver

- Split blade wedges into screw slot when collar is extended
- Holds screw in place when installing in hard to reach areas
- Easy to start screw when wearing gloves

Description	Cat. No.
1000V Insulated Screw Holding Screwdriver, 3/16 x 6 in. slotted Tip	35-9406