

Swivel-Blade Cable Stripper for 3/4 inch and smaller outside diameter cable

Catalog # 45-128



Features

- For single or multiple conductor cables up to 3/4 inch O.D.
- Blade adjusts for jacket thicknessess up to 1/8 inch

Tools and Totes

Cable Ripper

- Slits cable sheathing before stripping wires
- Quick, clean and easy end or mid-run removal of jacket
- Convenient built-in wire gauge

Description	Cat. No.
Side Entry Cable Ripper	45-118

Underground Feeder (UF) Cable Stripper

- Self-adjusting stripping blades automatically select proper position
- Strips 12 AWG solid to 14 AWG Underground Feeder (UF) Cable
- Strips Twin and Earth cable
- Open-throat construction allows unlimited strip length
- Neatly removes outer cable sheath and then inner wire sheathing to desired lengths
- Lightweight, ergonomic design reduces user fatigue

Description	Cat. No.
Underground Feeder Cable Stripper	45-235

Grip-N-Strip™ End Stripper

- Self-adjusting stripping blades automatically select proper position
- Strips 12 AWG solid to 20 AWG stranded PVC insulated wire
- Dual strip-length gauge marks at 3/16 in. and 5/16 in.
- Cuts up to 12 AWG solid wire
- Lightweight, ergonomic design reduces user fatigue
- Reinforced fiberglass construction
- Hardened steel blades for extra strength and longer life

Description	Cat. No.
Grip-N-Strip™ End Stripper	45-227

SIT NICKIESS Cutter

- Handles all common BX, MCAP, MC and Flex cables
- Blade cuts armor without damage to internal conductors
- Splices cleanly through casings with only a few turns



 Handle knob stores up to six replacement blades

Description	Cat. No.
Replacement blades (5/pack)	35-781
Rotary Armored Cable Cutter	35-782

Round Cable Slitting and Ringing Tool

- Cuts around cable jacket as well as slits the length of jacket for easy removal
- Use with single or multiple conductor cable up to 1.75 in. O.D.
- Blade adjusts for jacket thicknesses up to .125 in.
- Spare blade in handle base

Description	Cat. No.
Cable Stripper for 1/4 in. to 3/4 in. O.D.	45-128
Cable Stripper for 3/4 in. to 11/2 in. O.D.	45-129
Replacement Blades for 45-128 and 45-129 (2/pkg.)	L-7486

One-step stripping enchances productivty	A
Spring-action motion increases leverage and reduces operator fatigue	
Precision-ground, knife-type blades provide clean, accurate stripping	the second
Description	Cat. No. 🖤
Description Stripmaster® Wire Stripper, 10-22 AWG	Cat. No.

See Section D for complete Stripmaster® Wire Stripper line.

Stripmaster[®] Wire Strippers

C-7