

Stripmaster Wire Stripper #10 to #22 AWG

Catalog # 45-092




Features

- Knife-type blades
- Cleanly strips wire up to 7/8 in. (22mm)
- One-third less hand pressure for each strip
- Eliminates nicking, cutting, and fraying of wire
- Wire Gripper holds wire centered in hole

Tools and Totes

Cable Ripper





- Quick, clean and easy end or mid-run removal of jacket
- Convenient built-in wire gauge

Description	Cat. No.
Side Entry Cable Ripper	45-118

Underground Feeder (**UF**) **Cable Stripper**

- Self-adjusting stripping blades automatically select proper position
- Strips 12 AWG solid to 14 AWG Underground Feeder (UF) Cable
- Strips Twin and Earth cable
- Open-throat construction allows unlimited strip length
- Neatly removes outer cable sheath and then inner wire sheathing to desired lengths
- Lightweight, ergonomic design reduces user fatigue

Description	Cat. No.
Underground Feeder Cable Stripper	45-235

Grip-N-Strip™ End Stripper

- Self-adjusting stripping blades automatically select proper position
- Strips 12 AWG solid to 20 AWG stranded PVC insulated wire
- Dual strip-length gauge marks at 3/16 in. and 5/16 in.
- Cuts up to 12 AWG solid wire
- Lightweight, ergonomic design reduces user fatigue
- Reinforced fiberglass construction
- Hardened steel blades for extra strength and longer life

Description	Cat. No.
Grip-N-Strip™ End Stripper	45-227

SIT NICKIESS Cutter TO SEVER AND PROTECT RAMIORED CABLE

Handles all common BX, MCAP, MC and Flex cables

- Blade cuts armor without damage to internal conductors
- Splices cleanly through casings with only a few turns
- Handle knob stores up to six replacement blades




Description	Cat. No.
Replacement blades (5/pack)	35-781
Rotary Armored Cable Cutter	35-782

Round Cable Slitting and Ringing Tool

 Cuts around cable jacket as well as slits the length of jacket for easy removal

 Use with single or multiple conductor cable up to 1.75 in. O.D.



Spare blade in handle base

Description	Cat. No.
Cable Stripper for 1/4 in. to 3/4 in. O.D.	45-128
Cable Stripper for 3/4 in. to 11/2 in. O.D.	45-129
Replacement Blades for 45-128 and 45-129 (2/pkg.)	L-7486

Stripmaster® Wire Strippers

- One-step stripping enchances productivty
- Spring-action motion increases leverage and reduces operator fatigue
- Precision-ground, knife-type blades provide clean, accurate stripping

Cat. No.
45-NQ2

Description	Cat. No.
Stripmaster® Wire Stripper, 10-22 AWG	45-092
Stripmaster® Wire Stripper, Coax RG-6	45-262
Stripmaster® Wire Stripper, 10-22 AWG	45-292

See Section D for complete Stripmaster® Wire Stripper line.