

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

SHC1037CR -- Cord Connectors



Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue. They're available in N.P.

Product Specifications

Product Type	Cord Connectors
Material/Style	Nylon Standard Style
Cord Diameter Range	.63" - .75" (15.9- 19.0)
Cord Connector Body Style	Straight Male
Form Size	F3
HUB Size	3/4"
Color Code	Yellow
Effective Operating Temperature	-30°F to +225°F (-34°C to +107°C)
Recommended Knockout Hole Size	1.09" - 1.14" (27.8-29.0)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	1.56" (39.6) Dia.
Dimension B	1.60" (40.6) Ref.
Dimension C	.55" (14.0)
Dimension D	.77" (19.6) Throat Dia.
Dimension E A/C	1.44" (36.6)
Dimension E A/F	1.31" (33.3)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UPC Number	78358520809
Weight in LBs	0.3
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



