U.I. Lapp GmbH

PRODUCT INFORMATION



FLEXIMARK® NM Stainless steel - character holders

19.11.2014

FLEXIMARK® Character holder NM for assembly of characters made of acidproof stainless steel for cable and component marking in the electrical industry





Suitable for outdoor use



Cold-resistant



Corrosion-resistant



Acid-resistant



UV-resistant

Info

PR 10 NM 7 contained in FLEXIMARK® sample bag(article number M3251010)

Application range

Cable and component marking system For outdoor applications

Benefits

For mounting MR stainless steel characters Mounted with cable ties (maximum 7.9 mm width) or screws (up to 3 mm \varnothing) Acid-resistant

Product features

Holder for up to 46 characters

Remark

Photographs are not to scale and do not represent detailed images of the respective products. Contents: roll, metre, unit, marker, label

Technical Data

Info: Height: approx. 11 mm

Screw hole Ø: 3 mm

Material: Acid resistant stainless steel AISI 316-V4a

Temperature range: -80°C to +500°C

Product Management Document: LAPP_PRO1440EN.pdf 1 / 2

2/2

Product Management	
Document: LAPP_PRO1440E	

Part number	Article designation	Length (mm)	Characters/unit
83254214	FLEXIMARK® PR10 NM4	48,8	4
83254213	FLEXIMARK® PR10 NM5	60,4	8
83254212	FLEXIMARK® PR10 NM7	83,1	12
83254211	FLEXIMARK® PR10 NM9	109	16
83254210	FLEXIMARK® PR10 NM24	286	46

FLEXIMARK® NM Stainless steel - character holders PRODUCT INFORMATION 19.11.2014

MAPP GROUP

U.I. Lapp GmbH