



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7328: CN RELEASE, REVISED NOTES, FORMAT, PACKAGING, ROHS	3/7/14	D.FRISIELLO
F	ECN 7419: REVISED MATERIAL FOR FRONT AND REAR COVERS	5/20/14	D.FRISIELLO
G	ECN 7677: CHANGE REAR JACK HOUSING FROM PC/ABS TO ABS	11/12/14	D.FRISIELLO



NOTES:

MATERIAL:
 PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 JACK HOUSING FRONT: ABS, GRAY, PANTONE 423C
 JACK HOUSING REAR: ABS, GRAY, PANTONE 423C.
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PVC, SILVER SATIN

FINISH:
 CONTACTS: GOLD PLATING IN CONTACT AREA
 OVER NICKEL PLATE OVERALL.



WIRING MAP		
"J1"	COLOR	"P1"
1	WHITE	1
2	ORANGE	2
3	BLACK	3
4	RED	4
5	GREEN	5
6	YELLOW	6
7	BLUE	7
8	BROWN	8

CABLE CHARACTERISTICS:
 8 CONDUCTOR FLAT MODULAR CORD,
 U.L. STYLE 20251, 26 AWG STRANDED BARE COPPER.

MISCELLANEOUS:
 PLUG CONFORMS TO TIA-1096
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN
 ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D PARHAM	4/17/2001		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY T CLARK	4/24/2001	CATEGORY TELECOM/MODULAR	
	APPROVED BY R CARRICK	4/26/2001	PRODUCT DESCRIPTION EXTENDER, (8P8C) M/F STRAIGHT	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
REF	SCALE: NONE	CAD FILE: TAC535-8-7.SLDRW	DWG. NO. TAC535-8-7	REV. G
			SHEET 1 OF 1	