



Item No	Wire Size mm ²	L	C	D	French Colour	German Colour
E0206	0.25	6	0.8	1.1	VIOLET	LIGHT BLUE
E0208	0.25	8	0.8	1.1	VIOLET	LIGHT BLUE
E0306	0.34	6	0.8	1.1	PINK	TURQUOISE
E0308	0.34	8	0.8	1.1	PINK	TURQUOISE
E0506	0.5	6	1	1.3	WHITE	ORANGE
E0508	0.5	8	1	1.3	WHITE	ORANGE
E7506	0.75	6	1.2	1.5	BLUE	WHITE
E7508	0.75	8	1.2	1.5	BLUE	WHITE
E7513	0.75	12	1.2	1.5	BLUE	WHITE
E1006	1	6	1.4	1.7	RED	YELLOW
E1008	1	8	1.4	1.7	RED	YELLOW
E1012	1	12	1.4	1.7	RED	YELLOW
E1508	1.5	8	1.7	2	BLACK	RED
E1510	1.5	10	1.7	2	BLACK	RED
E1518	1.5	18	1.7	2	BLACK	RED
E2508	2.5	8	2.3	2.6	GREY	BLUE
E2512	2.5	12	2.3	2.6	GREY	BLUE
E2518	2.5	18	2.3	2.6	GREY	BLUE
E4009	4	9	2.8	3.2	ORANGE	GREY
E4012	4	12	2.8	3.2	ORANGE	GREY
E4018	4	18	2.8	3.2	ORANGE	GREY
E6012	6	12	3.5	3.9	GREEN	BLACK
E6018	6	18	3.5	3.9	GREEN	BLACK
E10-12	10	12	4.5	4.9	BROWN	IVORY
E10-18	10	18	4.5	4.9	BROWN	IVORY
E16-12	16	12	5.8	6.2	IVORY	GREEN
E16-18	16	18	5.8	6.2	IVORY	GREEN
E25-16	25	16	7.5	7.9	BLACK	BROWN
E25-22	25	22	7.5	7.9	BLACK	BROWN
E35-16	35	16	8.3	8.7	RED	BEIGE
E35-25	35	25	8.3	8.7	RED	BEIGE
E50-20	50	20	10.3	10.9	BLUE	OLIVE
E50-25	50	25	10.3	10.9	BLUE	OLIVE
E70-20	70	20	13.5	14.3	YELLOW	YELLOW