

MODEL 372-3—Ohmmeter, 0.2 to 50 M Ω

MADE IN

Provides a wide range of resistance measurements in a small package. 0.2 ohm to 50 megohms. Especially useful for checking submersible pumps. Ideal for use in schools, on test benches or at incoming inspection facilities.

• Ranges: 0-500 Ω ; 0-5 $K\Omega$; 0-50 $K\Omega$; 0-500 $K\Omega$; 0-5MEG Ω and 0-50 Meg Ω

Top Center Scale: 5Ω; 50Ω; 500Ω; 5ΚΩ
Bottom Center Scale: 30ΚΩ; 300ΚΩ
Accuracy: ± 3° of Linear Arc Length
Includes: Battery and Alligator Clip Leads

Range	Center (Ohms)	Maximum Current (Zero Ohms)	Maximum Voltage (Open Circuit)
RX1	5	340mA	1.5V
RX10	50	30mA	1.5V
RX100	500	3mA	1.5V
RX1000	5 K	0.3mA	1.5V
RX10K	30 K	0.65mA	21.5V
RX100K	300 K	65uA	21.5V



BATTERY REQUIRED: 1.5 "C", NEDA 14A (QTY: 1) 18V BATTERY ASSEMBLY (QTY: 1) Efficient Customer Service has been a valuable tool for generations of Simpson customers. Customer Service offers ongoing support for our products and calibration and repair service for all current test equipment. To obtain service for a discontinued Simpson product, contact Customer Service for assistance. We offer information regarding our capabilities and referrals to other service centers.

Call (715) 588-3311

Ordering Information

COMPACT METER	Catalog No.	ACCESSORIES	Catalog No.
372-3 Ohmmeter	12311	Case, Brown Padded Polyester	00836
		Leads	00125
		18V Battery Assembly	00840