

Datasheet

Stock No: 267-3701

ENGLISH

RS Pro SNYDL Series Insulated Crimp Spade Connector, 22 → 16 AWG, M3.5 (#6), Red Nylon



Product Details:

Spade

Red 0.5 - 1.5 mm² Blue 1 - 2.6 mm² Yellow 4.0 - 6.5 mm²

Approvals

UL Listed; UL Listed for Canada


Specifications:

Thickness:

Wire Size: $22 \rightarrow 16$ AWG


Stud Size: M3.5 (#6)
Width: 6.4mm
Insulation: Insulated

Colour: Red
Insulation Material: Nylon
Overall Length: 22mm
Series: SNYDL
Contact Material: Copper



Temperature rating:	-55°C to 105°C		
Terminal Material:			
Receptacles	High grade brass		
Other terminals	High grade copper		
Voltage rating			
Brass	300V		
Copper	600V		
Additional Sleeve Material:	High grade copper		

0.75mm



Type	Stud	Red		Blue		Yellow	
	Size	W	L	W	L	W	L
M8	8.4					14.0	30.2
M6	6.5	12.0	27.0	12.0	27.0	12.0	31.5
M5	5.3	9.5	20.9	9.3	20.9	9.0	25.2
M4.5	4.3	8.1	21.2	7.9	20.9	9.0	25.2
M4	4.3	7.2	21.2	7.2	21.2	8.3	25.2
M3.5	3.7	6.4	21.1	6.0	21.2	8.3	24.2
МЗ	3.2	5.7	21.1	5.6	21.0		