



Actual

Catalog Number: 25000
Product ID: 7TAA131180R0000
UPC Number: 78621025000
EAN Number: 05414363139270
Status: Active

Pneumatic Power Tool for Crimping D-M Non-insulated, RD-RM Insulated Terminals

- Compact Pneumatic Bench Mount, Shure-Stake Mechanism, Foot Pedal Operated

North American Specifications (UNSPSC)

UNSPSC	27111518 Wire lug crimping tool
IGCC	1967 Wire lug crimping tool
Brand Name	Sta-Kon
Type	Pneumatic Power Crimp Tool
Special Features	Compact Pneumatic Bench Mount, Shure-Stake Mechanism, Foot Pedal Operated
Standard	UL E9809

Packaging

Outer Quantity	1
Outer Dimensions (inches)	10x13.5x15.75
Weight Uom	44.8 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00571-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com