



# Facility, Security, and Pro AV

Rhino® 4200

All-Purpose Labeling Tool with QWERTY Keyboard



## Compact, time-saving labeling for on-the-go pros.

### Get labeling jobs done fast – and done right.

The new DYMO Rhino™ 4200 gets labeling jobs done fast – and done right. Easily navigate the familiar QWERTY keyboard. Use one-touch “Hot Key” shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 barcodes, fixed-length labels, breaker labels and more.

Print labels up to 3/4" wide in flexible nylon, permanent polyester and durable vinyl materials – PLUS print directly on heat-shrink tubes. Save even more time with great new features – like the ‘Favorites’ key which provides single-key access to commonly used labels, symbols and terms; and the ‘Custom’ key which eliminates repeated steps by saving customized settings.



### DYMO | Rhino 4200 features:

- 1 Easy to navigate computer-style QWERTY keyboard**  
Quick and comfortable text entry
- 2 One-Touch “Hot Keys” – a DYMO exclusive**  
Shortcut keys for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-length, general and breaker labels
- 3 Industrial-strength labeling versatility**  
Print 1/4", 3/8", 1/2" and 3/4" wide labels in a variety of materials and colors – PLUS print directly on heat-shrink tubes
- 4 NEW “Favorites” key**  
Single-key access to your most commonly used labels, symbols and terms
- 5 NEW “Custom” key prevents needless repetition**  
Customize and save settings for individual label formats



Up to



1" label widths not for use with the Rhino™ 4200

IND	LABEL APPLICATIONS	LABEL COLOR	1" label widths not for use with the Rhino™ 4200				
			1/4" 6mm	3/8" 9mm	1/2" 12mm	3/4" 19mm	1" 24mm
<b>Labels that stick and stay stuck.</b> DYMO Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labeling to OSHA, ISO and ANSI color standards or labeling in harsh conditions, DYMO Industrial labels have you covered. DYMO Industrial labels are designed to work exclusively with Rhino printers and to perform on a variety of surfaces. <a href="http://www.dymo.com/industrial">LEARN MORE: www.dymo.com/industrial</a>		BLACK ON WHITE	-	18443	18444	18445	1805430
		BLACK ON YELLOW	-	-	18432	18433	1805431
		BLACK ON ORANGE	-	-	18435	18436	1805427
		BLACK ON GREY	-	-	1805413	1805419	1805425
		WHITE ON RED	-	-	1805416	1805422	1805429
		WHITE ON BLACK	-	1805437	1805435	1805436	1805432
		WHITE ON GREEN	-	-	1805414	1805420	1805426
<b>VINYL</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 18'   5.5m 	WHITE ON BLUE	-	-	1805243	1805417	1805423
		WHITE ON PURPLE	-	-	1805415	1805421	1805428
		WHITE ON BROWN	-	-	1805412	1805418	1805424
<b>PERMANENT POLYESTER</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 18'   5.5m 	BLACK ON WHITE	1805442	18482	18483	18484	1734523
		BLACK ON CLEAR	1805440	18508DMO	622289	622290	1805433
		BLACK ON METALLIC	1805441	18485	18486	18487	1805434
<b>HEAT SHRINK TUBE</b> - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 	Length 5'   1.5m 	BLACK ON WHITE	18051	18053	18055	18057	-
		BLACK ON YELLOW	18052	18054	18056	18058	-
<b>FLEXIBLE NYLON</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 11.5'   3.5m 	BLACK ON WHITE	-	-	18488	18489	1734524
		BLACK ON YELLOW	-	-	18490	18491	1734525
<b>NON-ADHESIVE TAG</b> - RoHS compliant 	Length 18'   5.5m 	BLACK ON WHITE	18111	-	18113	-	-
<b>SELF-LAMINATING</b> - RoHS compliant 	Length 18'   5.5m 	BLACK ON WHITE	-	-	-	-	1734821

**RHINO 4200 SINGLE UNIT (BLISTER)**

Part No. 1801611  
 UPC: 0 71701 05959 8

**Box includes:**

- Rhino 4200 printer
- Quick Reference Guide
- 3/4" (19 mm) white flexible nylon tape

**Product specifications:**

- Runs on 6 AA batteries or optional rechargeable lithium-ion battery
- 1 year limited warranty
- Unit weight: 2 lbs.
- Units per master carton: 3
- Master carton dimensions (L x W x H) 9.9" x 9.0" x 11.6"
- Master carton weight: 6.55 lbs.

**Optional Accessories:**

- AC adapter Item# 15519
- Battery Item# 1759398

DYMO, the DYMO logo and Rhino are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners.

**Distributed by:**  
 DYMO, Atlanta, GA 30328  
 800-426-7827 www.dymo.com  
 © 2011 Sanford, L.P.



A **NewellRubbermaid** Brand