



Actual

Catalog Number: TCP360
Product ID: 7TAA159160R0000
UPC Number: 78621078784
EAN Number: 05414363162919
Status: Active

Deltec Modular Stackable Cable Spacer for Coaxial Cable, Black Polypropylene for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 53.34mm (2.1 Inches), Width of 30.48mm (1.2 Inches), Height of 12.7mm (0.50 Inches)

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Deltec
Type	Cable Spacers
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.
Material	Weather-Resistant Polypropylene
Color	Black
Tensile Strength	250 Pounds/1112 Newtons

European Specifications (ETIM)

ETIM	EC000127 Saddle
Material	Plastic
Material quality	Other
Surface protection	Untreated
Halogen free	Y
UV resistant	Y
Suitable in fire resistance areas	N
Plastic sheathed	N

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	15x12.5x9
Weight Uom	1.19 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com