



Actual

**Catalog Number:** TYD5270M  
**Product ID:** 7TAA159090R0010  
**UPC Number:** 78621071341  
**EAN Number:** 05414363067283  
**Status:** Active

Deltec Cable Tie with Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 685.80mm (27 Inches), Width of 12.7mm (0.5 Inches), Thickness of 1.52mm (0.06 Inches), Tensile Strength Rating of 1112 Newtons (250 Pounds), 25 Pack

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

### North American Specifications (UNSPSC)

|                  |  |
|------------------|--|
| UNSPSC           | 39121703 Cable ties  |
| IGCC             | 5034 Cable ties  |
| Brand Name       | Deltec   |
| Type             | Cable Tie  |
| Special Features | Perfect for coaxial, fiber optic and all other communication and electrical conducting cables. |
| Application      | Ideal solution for bundling in harsh outdoor environments.                                     |
| Width            | .500   |
| Length           | 27   |
| Material         | Weather Resistant Acetel   |
| Color            | Black  |
| Tensile Strength | 250 Pounds/1112 Newtons  |

### European Specifications (ETIM)

|                          |                        |
|--------------------------|------------------------|
| ETIM                     | EC000046 Cable tie     |
| Band width               | 12.7mm                 |
| Length belt/tape/tie     | 685.8mm                |
| Tie thickness            | 1.52mm                 |
| Max. bundle diameter     | 203.2mm                |
| Min. holding force       | 1112N                  |
| Operating temperature    | -40-+85°C              |
| Model                    | Internal toothing      |
| Band closure             | Double lock head       |
| Material                 | Plastic                |
| Material quality         | Polyoxymethylene (POM) |
| Surface protection       | Untreated              |
| Halogen free             | Y                      |
| Colour                   | Black                  |
| Transparent              | N                      |
| Reflective (fluorescent) | N                      |
| Text strip               | None                   |
| Solvable fastener        | N                      |
| Type of fastening        | None                   |
| MIL approval             | N                      |
| UL approval              | N                      |

### Packaging

|                           |                   |
|---------------------------|-------------------|
| Inner Quantity            | 10                |
| Outer Quantity            | 100               |
| Outer Dimensions (inches) | 34.25x6.5x5.25    |
| Weight Uom                | 5.75 lbs. per 100 |

## Documents / Support Tools

Technical Data Sheet CA Available on Website

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com