



Actual

Catalog Number: T28SST
Product ID: 7TAD013030R0013
UPC Number: 78620993143
Status: Active

3/4 Inch 316 Stainless Steel Form 8 (T) Conduit Body, Cover and Gasket with Polished Finish

- Available in body shapes LB, T, TB and LU® Universal Conduit Elbow
- Hub sizes from 1/2 inch to 2 inch
- Tapered (NPT) threads and integral bushings to protect wire insulation
- Ships complete with covers, gaskets and screws
- UL Listed and CSA Certified
- Connect conduit sections
- Act as pull outlets when conductors are being installed
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and light fixtures
- Provide access to conductors for maintenance and future system changes

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	T&B
Type	Form 8 Conduit Body
Special Features	Marine-Grade Type 316 Stainless Steel Construction In Rugged Form 8 Design
Application	Suitable for Use In Food and Beverage, Pharmaceutical, Petrochemical, Wastewater Treatment, Pulp and Paper Processing and Other Corrosive Environments
Standard	UL E2969, CSA
Hub Size	3/4 Inch
Form	8
Material	Stainless Steel
Finish	Polished

Packaging

Outer Quantity	1
Outer Dimensions (inches)	7.11x3.03x3.31
Weight Uom	1.92 lbs. Each

Documents / Support Tools

Technical Data Sheet Global wsd-000529

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

