

NOT for Patient-Care Rooms - UL1363 Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 10 ft. Cord, 1050 Joules

MODEL NUMBER: SPS610HGRA



Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 10-ft. cord with molded right-angle hospital-grade plug
- All metal housing

Package Includes

- SPS610HGRA Surge Suppressor
- Instruction manual with warranty information

Description

Our SPS610HGRA surge suppressor provides 6 hospital-grade outlets and protection from damaging surges and spikes with the added benefit of a convenient right-angle hospital-grade plug. The new design provides another option for convenient outlets outside the patient care area, including those tight spaces.

Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 10-ft. AC cord with integrated, molded right angle Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

MODEL TEXT



Key Benefit	Need to use a surge suppressor behind a desk or in a confined spot? The SPS610HGRA provides surge suppression with the convenience of a space-saving, right-angle hospital-grade plug for placing the units in confined areas and keyhole mounting tabs and flanges for easy installation.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R-HG
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 1 large transformer plug accessories without covering remaining outlets
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P-HG Hospital-Grade
Input Cord Length (ft.)	10
Input Cord Length (m)	4.6
Voltage Compatibility (VAC)	120
Maximum Surge Amps	19500
Right-Angle Plug	1
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED Details	LINE POWER PRESENT (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode surge suppression
Clamping Voltage (RMS)	140V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	2.25 x 15 x 6
Shipping Dimensions (hwd / cm)	5.7 x 38.1 x 15.24
Shipping Weight (lbs.)	3.5
Shipping Weight (kg)	1.59
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Includes keyhole mounting tabs and flanges
Receptacle Color	White
Color (AC Line Cord)	Gray
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>