



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Universal Computer Power Cord, 10A, 18AWG (NEMA 5-15P to IEC-320-C13), 6-ft.

MODEL NUMBER: **P006-006**



Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This 6 ft. cable will replace the power cable on most computers and peripherals that have a removable power cord. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. UL Listed.

Features

- 6 ft. NEMA 5-15P to IEC-320-C13 power cord
- 18AWG, SJT, 10A, 120V
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)

Highlights

- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device)
- 18AWG, SJT, 10A, 120V
- UL Listed

System Requirements

- Computer or peripheral with IEC-320-C14 computer style AC power plug

Package Includes

- 6-ft. Universal AC Power Replacement Cord, NEMA 5-15P Plug to IEC-320-C13 Receptacle



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	10 - 85% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>