



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™

DRILL/TAP, 10-24

10-24NC Drill/Tap Bit



Image
Unavailable

Cat No: 50176137

UPC No: 783310176138

Description

- Complete hole drilling, tapping and deburring/countersinking in one operation with power drill saves labor and time
- Back tapered beyond tap to prevent thread damage from over-drilling
- Deburr/countersink also provided on bit beyond back taper
- Made from hardened high-speed steel vs. carbon steel for longer life
- High quality hex shank to ensure strong connection to drill chuck
- Designed to tap up to 10-gauge metal
- Quick change adaptor included in both metric and standard kits

Specifications

- Material : High Speed Steel
- Material thickness : Up to 10 GA
- Material type : Mild Steel, Copper, Brass, Aluminum
- Point Type : Split Point With Web Thinning
- Shank : 1/4 IN Quick Change Hex
- Size : #10
- Thread Per Inch : 24 TPI
- Thread Type : NC