



File No. E205138
 Project No. 00CA03127

- **Case And Composition :** Acrylic resin front and bakelite case.
 Three studs mounting.
- **Accuracy :**
 AC class 2.0
 DC class 2.0
 Rectifier class 2.0
- **Color :** Black case and white scale plate.
- **Pointer :** Sword type color in black.

Measuring Ranges :

Moving Coil Type

DC uA	DC mA	DC A	DC mV	DC V
50	1	200	1	50
100	2	250	1.5	60
150	5	300	10	100
200	10	500	20	500
250	20	800	30	30
300	50		50	50
500	100		100	100
800	150		150	150

Moving Iron Type

AC mA	AC A	AC V
50	1	150
100	5	250
150	10	300
200	15	500
250	20	
300	30	
500	50	
800		

Rectifier Type

AC V
30
50
100
150
200
300
500

- **Hertz Meter :**
 Measuring Ranges : 45-65Hz, 45-55Hz, 55-65Hz
 Rated Voltage : 110V, 220V
 Accuracy : Class 2.0
 Consumption : Max. 15 mA
 Test Voltage : 2kV. 50-60Hz