

North American Region

[Download User Manual](#)

Recharge Value Charger

Product Detail:

Designation: Recharge Value Charger

Model: CHVCM3

Color: Black and White

Charge Capability: "AA" (2) or (4) / "AAA" (2) or (4)

"AA" (2) and "AAA" (2) Simultaneously

Note: Please note battery orientation diagrams in the instructions.



Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)
	AA	1300	5.0 hrs
	AA	2000	8.0 hrs
	AA	2300	10.0 hrs
	AAA	850	7.0 hrs

Shutoff Mechanism: Timer Control ~ 11 hrs
Delta V Detection

Charging Current: "AA" 260-300mA
"AAA" 120-150mA

Trickle Charge: None

Input Rating: 110-127VAC, 50/60Hz

Typical Weight: 107 grams (3.4 oz.)

Dimensions (mm): 115 x 71 x 62 (H x L x W)

Volume (cm³): 5062

Rev Polarity Protection: Yes

Primary Battery Detection: Yes

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.

CONVENIENT

- Charges 2 or 4 NiMH AA's or AAA's



SLEEK

- Sleek Design



EASY

- LED Indicators



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.

