


Hart lock industrial grade 50A locking devices

Product description


3-pole, 4-wire grounding
50A, 125/250V/AC
Non-NEMA, California standard



CS6365EX



CS6364EX



CS6376

California standard plugs & connectors

Rating A	V/AC	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
50	125/250	Pro grip nylon	0.44-1.06" (11.1-26.0mm)	RD & BK	□ CS6365EX	□ CS6364EX	•	•
		Armored	0.68-1.13" (17.3-28.6mm)	Steel	□ CS6365		•	•
		Armored	0.68-1.13" (17.3-28.6mm)	Steel		□ CS6364	•	•

California standard grade receptacles

Rating A	V/AC	Description	Color	Single receptacle		
50	125/250	California standard receptacles	BK	□ CS6369	•	•

California standard flanged inlets

Rating A	V/AC	Description	Color	Flanged inlet	Flanged inlet w/ lid		
50	125/250	California standard flanged inlets	Steel	□ CS6375	□ CS6376	•	•

Accessories for 50A California standard locking devices

Description	Color suffix	Catalog no.		
Weather protective glass-filled nylon, w/ lift lid cover	BK, CR, GY	□ 7788_	•	•
Weather protective diecast aluminum, w/ lift lid cover		□ 7770	•	
Weather protective boot for 50A armored plug		□ 7716	•	
Weather protective boot for 50A armored connector		□ 7717	•	
Weather protective boot for 50A pro grip plug		□ 7716EX	•	
Weather protective boot for 50A pro grip connector		□ 7717EX	•	



7788CR
Corrosion
resistant



7770



7716



7717



7716EX



7717EX

Dimensional information:

C-80, C-81

Plug & connector specification

50A pro grip: C-92
50A armored: C-92

Receptacle specification

50A: C-92

Flanged inlet & flanged outlet

specification information:
50A: C-92

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BK (Black), GY (Gray), RD (Red), Y or CR (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant - Page Q-30