Contact me about

this UPS



→ See All Eaton EX UPS Documentation

→ Back to Family Page

PULSI1500R-XL2U



Pulsar EX 1500 RT 2U is a high-performance Rack/Tower versatile UPS with high availability features and superb network management capabilities designed for small enterprise servers.

General

Topology On-line double conversion with automatic by-pass and power factor correction

Configuration Rack/Tower

PULSI1500R-XL2U Catalog Number

68184 Style Number Color metallic grey Rating (VA/Watts) 1500/1350

Dimensions (H x W x D, inches) 3.46 x 17.25 x 19

45 Weight (lbs)

Warranty Two-year factory warranty

Rail Kit Included Yes

Contents 1 ready-to-go UPS

(Ships with the following items) Power Management Software Suite CD USB Cable + Serial Cable DB9/DB9 (2) Brackets for 19" rack mounting

(2) Universal rails Hardware mounting kit Safety guide Quick Start

4-language user manual

Electrical Input

Connection (1) IEC-320-C14



Input Voltage Range $100/120/140/160\ V\ to\ 248V\ (Lower\ limits\ for\ <20\ \%,\ <33\ \%,\ <66\ \%,\ >=66\ \%\ of\ nominal\ power\ (VA).$ For\ active output\ power\ greater\ than

0.7 and 0.8 nominal rating, the lower limit is 180V and 190V respectively)

230 VAC Nominal Voltage 50/60 Hz Frequency Input frequency Range Without Using

Batteries

40 to 70 Hz

Electrical Output


Output Receptacles (6) IEC-320-C13



Power Factor

Load Segments 2 independent groups: 2 + 1 IEC C13 (10A) sockets

Battery



Optional Extended Battery Module

Battery Management

Battery Type

Programmable battery test, EXB auto recognition, automatic runtime adjustment, protection against deep discharge

Maintenance-free, sealed Lead-Acid battery

Communications

User Interface

(3) LEDs + adjustable multilingual display: display of measurements, access to control and setup menus

Communication Ports

(1) USB port, (1) RS232 serial port and relay contacts, (1) mini terminal block for remote On/Off and emergency stop

Communications Slot 1 Minislot for Network Management Card

Environmental & Standards

Audible Noise 45 dBA

Operating Temperature 32°F to 104°F (0°C to 40°C) continuous

Performance - Safety - EMC IEC/EN 62 040-3 (VFI-SS-113), IEC/EN 62 040-1-1, IEC/EN 60 950-1 (RD), IEC/EN 62 040-2 C1 Class

CE, TüV GS, CB report, UL 1778 cUL CSA 22.2 Approvals

Options

Services

Flex Plans

Onsite 1YR Service Coverage Onsite 2YR Service Coverage Onsite 3YR Service Coverage Onsite 5YR Service Coverage **Part Number**

List Price* FLN71XXX-1500UC

FLN72XXX-1500UC FLN73XXX-1500UC FLN75XXX-1500UC

-

Scheduled Onsite Services and Monitoring Part Number List Price' SU05NXXX-6009UC Onsite 7x24 Startup Onsite UPS PM 7x24 0005NXXX-6009UC eNotify Remote Monitoring Per Year XXXXNEXX-6009UC Scheduled Assembly Service 7x24 AS00NXXX-6009UC List Price* Extended Warranty Advanced Exchange Coverage for UPS (includes Battery in UPS) Part Number Warranty-3: 3-year-total warranty (UPS) for new product purchase 9SW3Y-1500UC Extend: 1-year warranty (UPS) for renewal extensions 9SW1Y-1500UC Warranty-5: 5-year-total warranty (UPS) for new product purchase 9SW5Y-1500UC **Extended Warranty Coverage for EBM (External Battery Module)** List Price* Part Number Warranty-3: 3-year- total warranty (EBM) 9SW3Y-3000BC Warranty-5: 5-year- total warranty (EBM) 9SW5Y-3000BC 9SW1Y-3000BC Extend: 1-year warranty (EBM) for renewal extensions

Batteries

Part Number List Price* Option Eaton EX 230V 1500 Rack EBM 68186

Extended Battery Module (EBM) for 230V Eaton EX 1000/1500VA Rack UPSs

Power Management Connectivity

Part Number List Price*

Network and MODBUS Card-MS MODBUS-MS Provides continuous, reliable and accurate remote monitoring of UPS systems

Network Card-MS Network-MS

Provides real time monitoring and control across UPSs in your network

Relay-MS

Enables automatic shutdown and network monitoring of a UPS system

Power Management Software



Intelligent Power Manager Enables monitoring and management of multiple network power devices and integrates seamlessly with VMware's vCenter Server and

66925 (Silver) Microsoft's SCVMM. View dem 66926 (Gold) Part Number List Price*

UPS Protection Software

free download

Intelligent Power Protector Provides automatic, graceful shutdown of PCs, servers and virtual machines during extended power outages. Compatible with ESXi, Hyper-V,

Xen and KVM. View demo

Power Distribution and Bypass

Part Number List Price* Option

ePDU, 0U, Basic, input C14, output (16) C13

* List Prices are not a reflection of the actual product Street Price. Check with your Eaton reseller or partner to get actual pricing.

Privacy Policy Terms & Conditions Copyright

 Φ

free download

ePBZ89

© 2013 Eaton All Rights Reserved