







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/23/11	D.GRIFFIN



MODEL NO.	LENGTH METERS [FEET]
HDRA-0.5	0.5 [1.64]
HDRA-1	1.0 [3.28]
HDRA-2	2.0 [6.56]
HDRA-3	3.0 [9.84]
HDRA-4	4.0 [13.12]
HDRA-5	5.0 [16.41]

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031. THE PACKAGE IS TO INCLUDE A STICKER THAT SAYS "HDMI HIGH SPEED WITH ETHERNET" PER THE HDMI LICENSING, LLC GUIDELINES. THE STICKER WILL BE CENTERED DIRECTLY UNDER THE L-COM LABEL.
- DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	9/21/11		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	9/21/11	CATEGORY VIDEO	
	APPROVED BY P. MCNEIL	9/21/11	PRODUCT DESCRIPTION CA HDMI-M/RA-M	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. HDRA	REV. A
			SCALE: NONE	CAD FILE: HDRA.SLDDRW
				SHEET 1 OF 1