



Actual

**Catalog Number:** HA 201  
**Product ID:** 7TAA010160R0000  
**UPC Number:** 78599141100  
**Status:** Active

Nipple, Chase Conduit, Trade Size 1/2 Inch, Zinc Alloy, For use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Steel City
Type	Chase Nipples
Application	For use with rigid/IMC conduits
Standard	UL E23018
Trade Size	1/2 Inch
Material	Zinc Die Cast

### European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Material housing	Other
Material quality	Other
Model	Straight
Material sealing	No sealing

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	7.625x4.125x3.875
Outer Quantity	1000
Outer Dimensions (inches)	20x9.25x8.25
Weight Uom	6.25 lbs. per 100

### Documents / Support Tools

Technical Data Sheet Global	wsd-001751
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)