



Representative

**Catalog Number:** DS3404MP000  
**Product ID:** 7TAA057020R0035  
**UPC Number:** 70891720860  
**Status:** Active

MaxGard Male Plug, 30 Amp, 3 Pole 4 Wire, 30 480V, 60Hz

### North American Specifications (UNSPSC)

UNSPSC	39121402 Electrical plugs
IGCC	4526 Electrical plugs
Brand Name	Russellstoll
Type	Russellstoll Hazardous Locations
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require air conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.
Standard	UL E68085
Material	Cast Aluminum

### European Specifications (ETIM)

ETIM	EC001322 Round socket/plug for high currents
Amperage	30A
Construction type	Plug
Number of poles	3

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	8.63x4.75x4.63
Weight Uom	2.72 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)