



Actual

**Catalog Number:** TYD10M  
**Product ID:** 7TAA159090R0007  
**UPC Number:** 78621098084  
**EAN Number:** 05414363933199  
**Status:** Active

Deltec Cable Tie with Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 635mm (25 Inches), Width of 12.7mm (0.5 Inches), Thickness of 1.52mm (0.06 Inches), Tensile Strength Rating of 1112 Newtons (250 Pounds)

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Deltec
Width	0.50 Inches/12.7mm
Length	25.0 Inches/635mm
Thickness	0.06 Inches/1.52mm
Material	Acetal (POM)
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	250 Pounds/1112 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	12.7mm
Length belt/tape/tie	635mm
Tie thickness	1.52mm
Min. holding force	1112N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Other
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x18x.04
Outer Quantity	250
Outer Dimensions (inches)	16.5x13.5x4.12
Weight Uom	2.13 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)