


For Patient-Care Vicinity – UL 1363A Medical-Grade Power Strip; 4 Hospital-Grade Outlets, 3 ft. Extendable Coiled Cord

MODEL NUMBER: PS-410-HGOEMCC



Description

The PS-410-HGOEMCC Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The coiled power cord is 3 ft. long, and can be fully extended to 10 ft.

Mounting flanges let you install the PS-410-HGOEMCC on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted
- 120V, 50/60 Hz power strip complies with UL 1363A specifications

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power

Highlights

- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 3 ft. coiled cord with NEMA 5-15P-HG hospital-grade plug extends to 10 ft.
- Features 4 NEMA 5-15R-HG hospital-grade outlets
- Easy to mount on a variety of surfaces

Package Includes

- PS-410-HGOEMCC UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 3 ft. Coiled, Extendable Cord
- Owner's Manual with maintenance requirements



- 3 ft. power cord is coiled so it can be extended up to 10 ft.
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Dual, resettable built-in 15A circuit breakers protect against dangerous overloads
- Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box

- Built-in mounting flanges make the PS-410-HGOEMCC easy to install on a variety of surfaces

Specifications

MODEL TEXT	
Key Benefit	Versatile power strip with coiled cord supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Orientation	Single row of 4
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	4.572
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	2.44 x 6.18 x 9.92
Shipping Dimensions (hwd / cm)	6.19 x 15.7 x 25.2
Shipping Weight (lbs.)	2.4
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	1.73 x 2.50 x 8.54
Unit Dimensions (hwd / cm)	4.39 x 6.35 x 21.69
Unit Weight (lbs.)	2.2
Unit Weight (kg)	1.0
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	77.60mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
CERTIFICATIONS	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>