



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Limit Switch Body

**E50SAL**

**UPC:**782113775364

### Dimensions:

- **Height:** 1.73 IN
- **Length:** 3.14 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Contact Rating:** 10A at 12 Vac, 1A at 125 Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Led Indicators:** LED indicator
- **Light Unit Voltage:** 24-120 Vac/dc
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Number Of Poles:** Single-pole
- **Operating Temperature:** -40° to 250°F (-40° to 121°C)
- **Series:** E50 Heavy Duty Plug In

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SAL](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data

