

**Datasheet** 

**Stock No: 267-3969** 

**ENGLISH** 

# RS Pro SNYDL Series Insulated Crimp Spade Connector, 12 → 10 AWG, M4 (#8), Yellow Nylon



### **Product Details:**

#### **Spade**

Red 0.5 - 1.5 mm<sup>2</sup> Blue 1 - 2.6 mm<sup>2</sup> Yellow 4.0 - 6.5 mm<sup>2</sup>

#### **Approvals**


UL Listed; UL Listed for Canada

## **Specifications:**


Wire Size:  $12 \rightarrow 10$  AWG

Stud Size: M4 (#8)
Width: 8.3mm
Insulation: Insulated
Colour: Yellow
Insulation Material: Nylon
Overall Length: 25.5mm
Series: SNYDL

Series: SNYDL
Contact Material: Copper
Thickness: 1mm



Temperature rating:	-55°C to 105°C		
Terminal Material:			
Receptacles	High grade brass		
Other terminals	High grade copper		
Voltage rating			
Brass	300V		
Copper	600V		
Additional Sleeve Material:	High grade copper		



Туре	Stud	Red		Blue		Yellow	
	Size	W	L	W	L	W	L
M8	8.4					14.0	30.2
M6	6.5	12.0	27.0	12.0	27.0	12.0	31.5
M5	5.3	9.5	20.9	9.3	20.9	9.0	25.2
M4.5	4.3	8.1	21.2	7.9	20.9	9.0	25.2
M4	4.3	7.2	21.2	7.2	21.2	8.3	25.2
M3.5	3.7	6.4	21.1	6.0	21.2	8.3	24.2
М3	3.2	5.7	21.1	5.6	21.0		