

Mechanical Pressure > General Purpose Gauges > 111.10

General Purpose Gauges - Black Plastic Case

Standard features

- | | |
|---|--|
| <ul style="list-style-type: none"> • Case: Black plastic • Wetted parts: Copper alloy • Window: Snap-in acrylic • Window ring: None • Dial: White plastic | <ul style="list-style-type: none"> • Color: Black plastic • Case fill: Not available • Accuracy: ±3/2/3% of span • Datasheet: 111.10 |
|---|--|



MECHANICAL PRESSURE

Type	111.10							
Size	1½"		2"		2½"		4"	
Connection	LM							
Conn. size	½" NPT		¼" NPT		¼" NPT		¼" NPT	
Press scale ¹	PSI	PSI	PSI	PSI/KPA	PSI	PSI/KPA	PSI	PSI/KPA
30" Hg	9747214	8990039	4252901	8990250	4253027	8990471	4255900	9767991
30"-0-15 psi					4253035	8990489	4255918	9768009
30"-0-30 psi					4253043	8990497	4255926	9768017
30"-0-60 psi					4253051	8990501	4255934	9768025
30"-0-100 psi					4253060	8990519	4255942	9768033
30"-0-160 psi					4253078	8990527	4255951	9768041
30"-0-200 psi					4253086	8990535	4255969	9768050
15 psi	9747222	8990102	4252919	8990323	4253108	8990552	4255977	9768068
30 psi	9747230	8990110	4252927	8990331	4253116	8990560	4255985	9768076
60 psi	9747249	8990128	4252935	8990349	4253124	8990578	4255993	9768084
100 psi	9747257	8990136	4252943	8990357	4253132	8990586	4256000	9768092
160 psi	9747265	8990145	4252951	8990365	4253141	8990595	4256018	9768106
200 psi	9747273	8990153	4252960	8990374	4253159	8990608	4256026	9768114
300 psi		8990161	4252978	8990382	4253167	8990616	4256034	9768122
400 psi			4252986		4253175	8990625	4256042	9768130
600 psi			4252994		4253183	8990633	4256051	9768149
800 psi					4253191	8990641	4256060	
1,000 psi			4253001		4253205	8990659	4256078	9768416
1,500 psi					4253213	8990667	4256086	
2,000 psi					4253221	8990675	4256094	
3,000 psi			4253019		4253230	8990684	4256107	
5,000 psi					4253248	8990692	4256115	

¹Vacuum scale: 30" Hg outside in black; 760 mm Hg inside in red.

Factory stocked items shown in **bold print**.

Items without part numbers are available - consult factory.

Reference pages 10 and 11 for 111.10 options.

Mechanical Pressure > General Purpose Gauges > 111.10

General Purpose Gauges - Black Steel Case

Standard features

- **Case:** Black steel
- **Wetted parts:** Copper alloy
- **Window:** Snap-in acrylic
- **Window ring:** None
- **Dial:** White plastic
- **Color:** Black plastic
- **Case fill:** Not available
- **Accuracy:** ±3/2/3% of span
- **Datasheet:** 111.10



Type	111.10		
Size	1½"	2"	2½"
Connection	LM		
Conn. size	½" NPT	¼" NPT	¼" NPT
Press scale ¹	PSI	PSI	PSI
30" Hg	50331841	4302192	4302397
30"-0-15 psi			
30"-0-30 psi			
30"-0-60 psi			
30"-0-100 psi			
30"-0-160 psi			
30"-0-200 psi			
15 psi	50630695	4302206	4302401
30 psi	50331787	4302214	4302443
60 psi	50331761	4302222	8991138
100 psi	50331884	4302231	8991146
160 psi	50331698	4302249	4302419
200 psi	50369377	4302257	8991162
300 psi		4302265	4302427
400 psi		4302273	4302435
600 psi		4302281	8991189
800 psi			
1,000 psi			
1,500 psi			
2,000 psi			
3,000 psi			
5,000 psi			8736499

¹Vacuum scale: 30" Hg outside in black; 760 mm Hg inside in red.

Factory stocked items shown in **bold print**
 Items without part numbers are available - consult factory.

Reference pages 10 and 11 for 111.10 options.

Mechanical Pressure > General Purpose Gauges > 111.10

General Purpose Gauges - Polished Brass Case

Standard features

- **Case:** Polished brass
- **Window:** Snap-in acrylic
- **Window ring:** Polished brass friction ring
- **Dial:** White plastic
- **Pointer:** Black plastic
- **Case fill:** Not available
- **Accuracy:** ±3/2/3% of span
- **Datasheet:** 111.10

Type	111.10
Size	2½"
Connection	LM
Conn. size	¼" NPT
Press scale ¹	PSI/KPA
30" Hg	8735980
30"-0-15 psi	8735999
30"-0-30 psi	8736006
30"-0-60 psi	8736049
30"-0-100 psi	8736014
30"-0-160 psi	8736022
30"-0-200 psi	8736030
30"-0-300 psi	
30"-0-400 psi	
15 psi	8736219
30 psi	8736227
60 psi	8736235
100 psi	8736243
160 psi	8736251
200 psi	8736260
300 psi	8736278
400 psi	8736286
600 psi	8736294
800 psi	8736308
1,000 psi	8738548
1,500 psi	8736464
2,000 psi	8736472
3,000 psi	8736480
5,000 psi	8736499



Additional scales available; contact factory for more information.

Factory stocked items shown in **bold print**
 Items without part numbers are available - consult factory.

Reference pages 10 and 11 for 111.10 options.