

Mechanical Pressure > Industrial Gauges > 213.40

Industrial Gauges - Forged Brass Case, Liquid-filled

Standard features

- **Case:** Forged brass
- **Window:** Acrylic
- **Window ring:** SS, crimped
- **Dial:** White aluminum
- **Color:** Black aluminum
- **Case fill:** Glycerine
- **Accuracy:** ±2/1/2% of span (2½" size)
±1% of span (4" size)
- **Datasheet:** 213.40



Type	213.40									
	2½"						4"			
Size	LM			CBM			LM		LBM	
Connection	LM			CBM			LM		LBM	
Conn. size	¼" NPT						¼" NPT	½" NPT	¼" NPT	½" NPT
Press scale ¹	PSI	PSI/KPA	PSI/BAR	PSI	PSI/KPA	PSI/BAR	PSI	PSI	PSI	PSI
30" Hg	9318003	9456198	9734109	9318070	9455930	9734312	9314555		9314296	
30"-0-15 psi	9318011	9613862		9318089	9325662		9314563		9314300	
30"-0-30 psi	9318020	9456163		9318097	9325689		9314571		9314318	
30"-0-60 psi	9318038	9456201		9318100	9325816		9314580		9314326	
30"-0-100 psi	9318046	9679928		9318119	9149872		9314598		9314334	
30"-0-160 psi	9318054	9679936		9318127	9325972		9314601		9314342	
30"-0-200 psi	9318062	9442863		9318135	9326251		9314610		9314350	
15 psi	9310673	9456155	9734117	9318143	9455949	9734215	9314644	9314121	9314385	
30 psi	9310681	9456171	9734125	9318151	9455957	9734223	9314652	9314130	9314393	
60 psi	9310690	9456210	9734134	9318160	9455965	9734231	9314660	9314148	9314407	
100 psi	9310703	9456228	9734142	9318178	9456120	9746072	9314679	9314156	9314415	
160 psi	9310711	9456180	8986216	9318186	9455981	9734257	9314687	9314164	9314423	
200 psi	9310720	9456236		9318194	9442979		9314695	9314172	9314431	
300 psi	9310738	9442871	9798870	9318208	9442987	9734265	9314709	9314180	9314440	
400 psi	9310746	9611452		9318216	9455990		9314717	9314199	9314458	
600 psi	9310754	9456244	8985815	9318224	9456007	8985774	9314725	9314202	9314466	
800 psi	9310762	9690115		9318232	9128832		9314733	9314210	9314474	
1,000 psi	9310770	9456252	9798404	9318240	9456015	9746048	9314741	9314229	9314482	
1,500 psi	9310789	9456260	9734193	9318259	9207511	8985829	9314750	9314237	9314490	9324143
2,000 psi	9310797	9455906		9318267	9456023		9314768	9314245	9314504	9325026
3,000 psi	9310800	9455914	8985566	9318275	9435220	8985831	9314776	9314253	9314512	9480609
5,000 psi	9310819	9456279		9318283	9442995		9314784	9314261	9314520	9413448
7,500 psi	9325107	9455922		9318291	9128840					
10,000 psi	9790454						9314792	9314270	9314539	9413960
15,000 psi										

¹ Vacuum scale: 30" Hg outside in black; 760 mm Hg inside in red.

Factory stocked items shown in **bold print**.
Items without part numbers are available - consult factory.