






INDUSTRIAL GAUGES

Mechanical Pressure > Industrial Gauges > 233.53, 232.53 Ammonia

MECHANICAL PRESSURE

Type	233.53 (Glycerine filled)				
Size	2 1/2"		4"		
Connection	LM 	CBM 	LM 	LBM 	
Conn. size	1/4" NPT		1/4" NPT	1/2" NPT	
Press scale ¹	PSI	PSI	PSI	PSI	PSI
30" Hg	9833646	9833310	9833124	9833328	9831504
30"-0-15 psi			9831775	9833336	9831512
30"-0-30 psi	9833638	9833302	9832993	9833345	9831520
30"-0-60 psi	9833620	9833298	9833000	9833353	9831538
30"-0-100 psi			9831759	9831741	9831546
30"-0-160 psi	9833612	9833280	9833018	9833361	9831555
30"-0-200 psi			9831767	9833379	9831563
15 psi	9833604	9833272	9833026	9833387	9831571
30 psi	9833590	9833264	9833035	9833395	9831589
60 psi	9833582	9833255	9833043	9833409	9831597
100 psi	9833574	9833247	9833051	9833417	9831601
160 psi	9833565	9833239	9833069	9833425	9831619
200 psi	9833557	9833221	9833077	9833434	9831627
300 psi	9833549	9833213	9833085	9833442	9831635
400 psi	9833531	9833205	9833094	9833450	9831644
600 psi	9833523	9833191	9833107	9833727	9831652
800 psi					
1,000 psi	9833515	9833183	9833115	9833697	9831678
1,500 psi	9833506	9833175		9833701	9831686
2,000 psi	9833493	9833166		9833655	9831695
3,000 psi	9833485	9833158		9833719	9831708
5,000 psi	9833476	9833140		9833663	9831716
10,000 psi	9833468	9833132		9833671	9831725
15,000 psi				9833689	9831733

Type	232.53	
Category	Ammonia Gauges	
Connection	LM 	
Size	2 1/2"	4"
Conn. size	1/4" NPT	
Press scale ¹	PSI/°F	PSI/°F
30"-0-150 psi / 84°F	9797144	9797127
30"-0-300 psi / 126°F	9797152	9797135

¹Vacuum scale: 30" Hg outside in black; 760 mm Hg inside in red.

Factory stocked items shown in **bold print**.
Items without part numbers are available - consult factory.