

Accessories

Metal Enlargers



Nickel plated brass fittings, PG to PG, PG to metric, metric to PG

Metric & PG Thread

Enlargers are ideal when a threaded hole exists and you need to secure a larger thread or different style of thread. Made of nickel plated brass, SAB's enlargers are very durable.

Technical data:

Material:	Brass, Nickel Plated
Attachment thread:	EN 60423 (Metric); DIN 40430 (PG)



Part Number	Thread Type OT (male)	Thread Type IT (female)	Inner Thread Length ITL inches	Outer Thread Length OTL inches	Outer Diameter OD inches	Inner Diameter ID inches	Height (H) inches
PG-PG							
ENL-01	PG 7	PG 9	0.197	0.197	0.669	0.315	0.394
ENL-02	PG 9	PG 11	0.276	0.236	0.787	0.453	0.413
ENL-03	PG 9	PG 13.5	0.354	0.236	0.866	0.453	0.453
ENL-04	PG 11	PG 13.5	0.335	0.709	0.866	0.543	0.453
ENL-05	PG 11	PG 16	0.335	0.866	0.945	0.543	0.413
ENL-06	PG 11	PG 21	0.394	1.063	1.181	0.543	0.571
ENL-07	PG 13.5	PG 16	0.335	1.339	0.945	0.650	0.413
ENL-08	PG 13.5	PG 21	0.394	1.654	1.181	0.650	0.571
ENL-09	PG 16	PG 21	0.394	1.102	1.169	0.689	0.472
ENL-10	PG 16	PG 29	0.472	2.047	1.575	0.689	0.630
ENL-11	PG 21	PG 29	0.551	2.559	1.535	0.945	0.630
ENL-12	PG 29	PG 36	0.689	0.315	1.969	1.260	0.768
ENL-13	PG 36	PG 42	0.748	0.354	2.244	1.496	0.866
ENL-14	PG 42	PG 48	0.768	0.394	2.520	1.937	0.906
PG-Metric							
ENL-47	PG 7	M12x1.5	0.276	0.197	0.551	0.315	0.394
ENL-48	PG 9	M16x1.5	0.315	0.236	0.709	0.453	0.433
ENL-49	PG 11	M20x1.5	0.335	0.236	0.866	0.571	0.453
ENL-50	PG 13.5	M20x1.5	0.335	0.256	0.866	0.650	0.453
ENL-51	PG 16	M25x1.5	0.335	0.256	1.063	0.689	0.492
ENL-52	PG 21	M32x1.5	0.472	0.276	1.339	0.945	0.630
ENL-53	PG 29	M40x1.5	0.591	0.315	1.654	1.260	0.768
ENL-54	PG 29	M50x1.5	0.630	0.315	2.126	1.260	0.768
Metric-PG							
ENL-15	M12x1.5	PG 9	0.276	0.236	0.669	0.315	0.354
ENL-16	M16x1.5	PG 11	0.295	0.236	0.787	0.472	0.354
ENL-17	M20x1.5	PG 16	0.335	0.315	0.945	0.630	0.413
ENL-45	M25x1.5	PG 16	0.531	0.315	2.126	1.024	0.669
ENL-18	M25x1.5	PG 21	0.394	0.354	1.181	0.787	0.492
ENL-19	M32x1.5	PG 29	0.512	0.315	1.575	1.083	0.630
ENL-20	M40x1.5	PG 36	0.551	0.354	1.969	1.398	0.728
ENL-21	M50x1.5	PG 42	0.709	0.354	2.244	1.791	0.866
ENL-22	M63x1.5	PG 48	0.709	0.354	2.520	2.205	0.906

N

29