



Tripp Lite
 1111 West 35th Street
 Chicago, IL 60609 USA
 Telephone: +(773) 869 1234
 E-mail: saleshelp@tripplite.com

Model #: P006-004

4-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)



Highlights

- UL and CSA listed
- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device)
- 18AWG (0.824mm²), SJT, 10A, 125V

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This 4ft cable will replace the power cable on most computers and peripherals that have a removable power cord. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. Cable has both UL and CSA approvals.

Package Includes

- 4-ft. Universal AC Power Replacement Cord, NEMA 5-15P Plug to IEC-320-C13 Receptacle

Features

- UL-listed, CSA approved
- 4-ft. replacement power cable for a PC, printer, monitor or any other device with like plugs
- Universal design
- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device)
- 18AWG (0.824mm²), SJT, 10A, 125V

Specifications

OVERVIEW	
Intended Application	Powering Devices
Model Type	Power Cords
INPUT	
Cable Length (ft.)	4
Cable Length (m)	1.22
PHYSICAL	
Color	Black

Style	Power Cables
CONNECTIONS	
Connector A	NEMA 5-15P
Connector B	IEC-320-C13
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
P006-003	3-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-006	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4614.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.