



SURGE SUPPRESSOR, RC COUPLING,
AC 127...240V, DC 150...250V,
F. CONT. RELAYS A. MOTOR CONT. SZ S00,

General technical data:

product brand name		SIRIUS
product designation		surge suppressor
Size of the contactor		S00
Design of the surge suppressor		with RC elements
Ambient temperature		
• during storage	°C	-40 ... +80
• during operating	°C	-25 ... +60

Control circuit:

Type of voltage / of the controlled supply voltage		AC/DC
Control supply voltage frequency		
• 1 / rated value	Hz	50
• 2 / rated value	Hz	60
Control supply voltage / 1		
• for DC		
• initial rated value	V	150
• final rated value	V	250
• at 50 Hz / for AC		
• initial rated value	V	127
• final rated value	V	240





- at 60 Hz / for AC
 - final rated value
 - initial rated value

V	240
V	127

Installation/mounting/dimensions:

mounting position		any
Type of mounting		clip-on
Width	mm	28
Height	mm	46
Depth	mm	9

Certificates/approvals:

Verification of suitability	CE / UL / CSA / CCC	
General Product Approval	Declaration of Conformity	Test Certificates
 CSA  GOST  UL	 EG-Konf.	Special Test Certificate

Shipping Approval



Shipping Approval other



Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator



<http://www.siemens.com/cax>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WWW/view/en/3RT2916-1CD00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RT2916-1CD00





last change:

Jun 22, 2012