Contactors and Contactor Assemblies

3RT Contactors / 3RH Control Relays

SIRIUS

Selection and ordering data

Accessories for contactors, control relays and auxiliary contactors













3RH19 11-1HA -1FA..

3RH19 11-2HA. -2FA..

3RH19 21-1HA..

3RH19 21-2HA...

3RH19 11-1AA

3RH19 11-1LA.

	ated operational urrent ²)	Auxiliary	contacts	Screw connection		Cage Clamp connection	า	Weight approx.
Type	EMA A600 / Q600	Ident. no.	Design	Order No.	List Price \$	Order No.	List Price \$	kg

Auxiliary switch blocks for snapping onto the front acc. to EN 50 012 $^{\rm 1})$

Size S00

For making contactors with 2, 4 or 5 auxiliary contacts

Sizes S0 to S121)	32 E	 -2	_	_	3RH19 11-1HA22	28.00	3RH19 11-2HA22	32.00	
4-pole									

3RT10 2,		31	3	1	_	-	3RH19 21-1HA31	40.00	3RH19 21-2HA31	44.00	0.065
3RT1. 3 to		22	2	2	_	-	3RH19 21-1HA22	40.00	3RH19 21-2HA22	44.00	
3RT1.7,		13	1	3	_	-	3RH19 21-1HA13	40.00	3RH19 21-2HA13	44.00	
3RT11	and the first and the second states	00	0	0			0D1140 04 4V400 08440	44.00	001140 04 0VA00 01440	40.00	
	with location digits	22	2	2	_	-	3RH19 21-1XA22-0MA0	44.00	3RH19 21-2XA22-0MA0	48.00	
	5, 6, 7, 8										

Auxiliary switch blocks for snapping onto the front acc. to EN 50 005 $^{\rm 1})$

Size S00

	2 or 4-pole auxiliary	switch b	locks	s for I	making co	ontactors with 3 or 5 auxili	ary contacts		
3RT1. 1, 3RH11, 3RH14	1	20 ∣1)2 ∣1 U	2	 1 - 2 - - 1	- - - 1	3RH19 11-1FA20 3RH19 11-1FA11 3RH19 11-1FA02 3RH19 11-1FB11	14.00 14.00 14.00 14.00	3RH19 11-2FA11 10 3RH19 11-2FA02 10	6.00 0.045 6.00 6.00 0.00
	3 2 2	81	4 3 2 -	 1 - 2 - - 2 1 1	- - - 2 2 1	3RH19 11-1FA40 3RH19 11-1FA31 3RH19 11-1FA22 3RH19 11-1FC22 3RH19 11-1FB22	28.00 28.00 28.00 42.00 42.00	3RH19 11-2FA31 32 3RH19 11-2FA22 32	2.00 0.045 2.00 2.00 6.00
	Single or 2-pole auxil Cable entry from about		tch b	lock	s, cable e	ntry from one side			
	- - - -	- - -	1 - 1 2	1 - 1 - 	 	3RH19 11-1AA10 3RH19 11-1AA01 3RH19 11-1LA11 3RH19 11-1LA20	10.00 10.00 14.00 14.00	- - -	0.015
	 Cable entry from be 	elow							
	- - -	- -	1 - - 1	 1 - 1 -	- - -	3RH19 11-1BA10 3RH19 11-1BA01 3RH19 11-1MA11	10.00 10.00 14.00	_	0.015 0.045
	_	_	2		_	3RH19 11-1MA20	14.00	_	2.0.10

EN50005 and EN50012 designate the markings of the auxiliary terminal numbers. For position of the terminals see pages 2/154-156. For int. circuit diagrams see pages 2/150-151

- 1) Exception: 3RT16.
- 2) UL ratings on page 19/18 in section 19.

Contactors and Contactor Assemblies

3RT1 Contactors

Accessories for contactors

Selection and ordering data













3RH19 21-2F...

3RH19 21-1LA.

3RH19 21-1MA.

For contactors	Rated operational current ²)	Auxiliary	contacts	Screw connection	on	Cage Clamp conn	ection	Weight approx.	Pack.
	NEMA A600 / Q600	Ident. no.	Design	Order No.	List Price \$	Order No.	List Price \$		
Туре			NO NC NO NC					kg	

Auxiliary switch blocks for snapping onto the front acc. to EN 50 005

Sizes S0 to S121)

4-pole auxiliary switch blocks

3RT10 2, 3RT1. 3 to 3RT1. 7, 3RT11	Single-pole auxilia	40 31 22 04 22 U	4 3 2 - -	1 2 4 -	- - - 2	- - - 2	3RH19 21-1FA40 3RH19 21-1FA31 3RH19 21-1FA22 3RH19 21-1FA04 3RH19 21-1FC22	40.00 40.00 40.00 40.00 54.00	3RH19 21-2FA40 3RH19 21-2FA31 3RH19 21-2FA22 3RH19 21-2FA04 3RH19 21-2FC22	44.00 44.00 44.00 44.00 58.00	0.065	1 unit
3RT1. 2 to 3RT1. 7, 3RT11	Single-pole auxilia	- - - -	1 - -	1 - -	- - 1 -	- - - 1	3RH19 21-1CA10 3RH19 21-1CA01 3RH19 21-1CD10 3RH19 21-1CD01	10.00 10.00 20.00 20.00	3RH19 21-2CA10 3RH19 21-2CA01 -	11.00 11.00	0.015	1 unit
3RT10 2,	2-pole auxiliary sw • Cable entry from		1	ith c	able -	entry from	3RH19 21-1LA11	20.00	-		0.065	1 unit
3RT1. 3 to 3RT1. 7, 3RT11	Cable entry from	- below	2	2	=	_	3RH19 21-1LA20 3RH19 21-1LA02	20.00	-			
		<u>-</u>	1 2 -	1 - 2	- - -	- - -	3RH19 21-1MA11 3RH19 21-1MA20 3RH19 21-1MA02	20.00 20.00 20.00	-		0.065	1 unit

EN50005 and EN50012 designate the markings of the auxiliary terminal numbers.
For position of the terminals see pages 2/154-156.
For int. circuit diagrams see pages 2/149-151.


¹⁾ Exception: 3RT16.

²⁾ UL ratings on page 19/18 in section 19.



Accessories for contactors

Selection and ordering data



EN50005 and EN50012 designate the markings of the auxiliary terminal numbers. For position of the terminals see pages 2/154-157. For int. circuit diagrams see pages 2/150-151.

¹⁾ UL ratings on page 19/18 in section 19.

Contactors and Contactor Assemblies

3RT1 Contactors and 3RH1 Control Relays



Accessories for contactors and control relays

Selection and ordering data











3RH19 11-1NF.

3RH19 11-2NF..

3RH19 21-1FE22

3RH19 21-2FE22

3RH19 21-2DE11 -2JE11

For contactors / control relays	Design	Contacts	Screw connection		Cage Clamp conne	Weight approx.	
_		Design	Order No.	List Price \$	Order No.	List Price \$	
Type		NO NO NC NC					kg

Solid-state compatible auxiliary switch blocks for snapping onto the front, acc. to EN 50 005

Size S00

Sizes S0 to	at 3 V to 60 V. Hard gold-plated contacts.No positively driven operation									
3RH14	currents from 1 mA to 300 mA	_		=	2	3RH19 11-1NF02	63.00	3RH19 11-2NF02	65.00	
3RT1.1, 3RH11,	For use in dusty atmosphere and electronic circuits with rated operational	1 2	_	_	1	3RH19 11-1NF11 3RH19 11-1NF20	63.00 63.00	3RH19 11-2NF11 3RH19 11-2NF20	65.00 65.00	0.045

3RT1 . 2 to 3RT1 . 7	1 NO + 1 NC solid-state compatible auxiliary switches: For use in dusty atmosphere and elec- tronic circuits with rated operational currents 1 mA to 300 mA at 3 V to 60 V. Hard gold-plated contacts.	1	1	1	1	3RH19 21-1FE22	79.00	3RH19 21-2FE22	79.00	0.065
	1 NO + 1 NC standard auxiliary switches: For technical data, see page 2/91.									

Solid-state compatible auxiliary switch blocks, laterally mountable, acc. to EN 50 012

Sizes S0 to S12

• First laterally mountable auxiliary switch block (right or left), 2-pole

3RT1.2	1 NO + 1 NC solid-state compatible	1	_	-	1	-		3RH19 21-2DE11	58.00	0.038
to	auxiliary switches:									
3RT1.7	For use in dusty atmosphere and elec-									
	tronic circuits with rated operational									
	currents from 1 mA to 300 mA									
	at 3 V to 60 V.									
	Hard gold-plated contacts.									

Sizes S3 to S12

	 Second laterally mountable auxilia 										
3RT1. 4 to 3RT1. 7	1 NO + 1 NC solid-state compatible auxiliary switches: For use in dusty atmosphere and electronic circuits with rated operational currents from 1 mA to 300 mA at 3 V to 60 V. Hard gold-plated contacts.		=	_	1		-	3F	H19 21-2JE11	75.00	0.038

EN50005 and EN50012 designate the markings of the auxiliary terminal numbers. For position of the terminals see pages 2/154-156. For int. circuit diagrams see pages 2/150-151.