## Pushbutton Units and Indicator Lights 30 mm Heavy Duty, Watertight/Oiltight, Class 52

Push pull complete units

#### Selection and ordering data

	Version	Color of actuator	Contact blocks	Order no.	List Price	Order no.	List Price	Pac
		dotadior	01001/3	Plastic Head	\$	Metal Head	\$	Uni
Position push-pull on-illuminated	2 Position Push Pull, Maintained <sup>®</sup> Non-Illuminated							
	1 3/4" (44.5 mm) mushroom head	less operating	1NO - 1NC	52PP2WZA		52PP2AZA		1
		head red green yellow chrome	1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2W2A 52PP2W3A 52PP2W4A —		52PP2A2A 52PP2A3A  52PP2ACA		
- The	2 1/2" (63.5 mm) mushroom head	less operating	1NO - 1NC	52PP2VZA				
		head red green yellow chrome	1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2V2A 52PP2V3A 52PP2V4A 				
Position push-pull	3 Position Push Pull, Momentary				-		-	
ion-illuminated	Non-Illuminated (Pull to start, push to stop) <sup>①</sup>							
	1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP3WZU		52PP3AZU		
OD		red green yellow chrome	1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3W2U 52PP3W3U 52PP3W4U 		52PP3A2U 52PP3A3U  52PP3ACU		
						021107000		
	2 1/2" (63.5 mm) mushroom head	less operating head red green yellow chrome	1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3VZU 52PP3V2U 52PP3V3U 52PP3V4U —				
	3 Position Push Pull, Push Maintained, Pull Momentary Non-Illuminated (Pull to start, push to stop) <sup>①</sup>							
	1 3/4" (44.5 mm) mushroom head	less operating	1NO - 1NC	52PP7WZU		52PP7AZU		
		head red green yellow chrome	1NO - 1NC 1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7W2U 52PP7W3U 52PP7W4U —		52PP7A2U 52PP7A3U  52PP7ACU		
	2 1/2" (63.5 mm) mushroom head	less operating head	1NO - 1NC	52PP7VZU				
		red	1NO - 1NC	52PP7V2U				
		green	1NO - 1NC	52PP7V3U				
		yellow chrome	1NO - 1NC 1NO - 1NC	52PP7V4U —				
	Color options <sup>®:</sup>	black blue grey orange		1 5 6 8				

Technical Specifications on page 10/169A

⑦ Blocks cannot be interchanged (start-stop circuit).
② To order a color option, replace the 7th digit of the order number.

-stop circuit). (3) EMERGENCY-STOP control devices according to IEC 60947-5-5 when provided with red operating head and 52BJK contact blocks.

### Push pull complete units

# • Revised • 03/20/2012

	Selection and	ordering data
--	---------------	---------------

	Version	Color of Contact actuator blocks		Order no.	List Price	Order no.	List Price	Pack
		actuator	DIUUNO	Plastic Head	\$	Metal Head	\$	Unit
2 Position push-pull illuminated	2 Position Push Pull, Maintained <sup>®</sup> Illuminated, Integrated LED Module							
(CO)	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2LRA 52PP2LSA 52PP2LTA		52PP2L2A 52PP2L3A 52PP2L9A		1
	120 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2MRA 52PP2MSA 52PP2MTA		52PP2M2A 52PP2M3A 52PP2M9A		1
	240 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2NRA 52PP2NSA 52PP2NTA		52PP2N2A 52PP2N3A 52PP2N9A		1
	2 Position Push Pull, Maintained $^{\textcircled{M}}$ Illuminated, Full Voltage $^{\textcircled{M}}$							
	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP2DZA		-		1
	with 52AADN, 24 V 757 type lamp or option: B = 52AED*, 24 V Single LED <sup>®</sup>	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2DRA 52PP2DSA —		52PP2D2A 52PP2D3A 52PP2D9A		
	2 Position Push Pull, Maintained $^{\textcircled{3}}$ Illuminated, Transformer $^{\textcircled{3}}$							
	120 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP2GZA		-		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2GRA 52PP2GSA 52PP2GTA		52PP2G2A 52PP2G3A 52PP2G9A		
	240 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP2HZA		-		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED <sup>®</sup>	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2HRA 52PP2HSA 52PP2HTA		52PP2H2A 52PP2H3A 52PP2H9A		
	480 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP2JZA		-		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED <sup>®</sup>	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2JRA 52PP2JSA 52PP2JTA		52PP2J2A 52PP2J3A 52PP2J9A		
	600V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP2KZA		-		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP2KRA 52PP2KSA 52PP2KTA		52PP2K2A 52PP2K3A 52PP2K9A		
	Color option	ns <sup>@:</sup> blue clear white				5 A B		

Technical Specifications on page 10/169A

- ① LED option available. For single LED only, append B to the end of the ordernumber. Single LEDs available for all colors. LED color and lens color must match.LED option is not available on units sold "less operating head". Example: Single LED: 52PP2HRAB
- (2) To order a color option, replace the 7th digit of the order number.
- ③ Replace asterisk (\*) in LED part number with color option that matches lens. See replacement lamps on page 10/161, for complete catalog number.
- ④ EMERGENCY-STOP control devices according to IEC 60947-5-5 when provided with red operating head and 52BJK contact blocks.
- (b) Full Voltage modules are available with additional voltage ratings from the factory. For Incandescent lamps change the 6th Character to B=6V, C=12V, or E=120V (Example: Order 52PP2B2A for 6V Incandescent Lamp). For LED options change the 6th Character to B=6V AC, or E=120V AC (Example: Order 52PP2B2AB for 6V AC LED Lamp option).

## Pushbutton Units and Indicator Lights 30 mm Heavy Duty, Watertight/Oiltight, Class 52

### Push pull complete units

#### Selection and ordering data

	Version	Color of Contact		Order no.	List	Order no.	List	Pack
		actuator	blocks	ordor no.	Price	ordor no.	Price	1 don
				Plastic Head	\$	Metal Head	\$	Unit
3 Position push-pull illuminated	3 Position Push Pull, Momentary Illuminated, Integrated LED Module							
1000	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3LRU 52PP3LSU 52PP3LTU		52PP3L2U 52PP3L3U 52PP3L9U		1
	120 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3MRU 52PP3MSU 52PP3MTU		52PP3M2U 52PP3M3U 52PP3M9U		1
	240 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3NRU 52PP3NSU 52PP3NTU		52PP3N2U 52PP3N3U 52PP3N9U		1
	<b>3 Position Push Pull, Momentary Illuminated, Full Voltage</b> ® (Pull to start, push to stop)®							
	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP3DZU		52PP3DZU		1
	with 52AADN, 24 V 757 type lamp or option: B = 52AED*, 24 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3DRU 52PP3DSU 52PP3DTU		52PP3D2U 52PP3D3U 52PP3D9U		
	3 Position Push Pull, Momentary Illuminated, Transformer $^{\mbox{O}}$ (Pull to start, push to stop) $^{\mbox{O}}$							
	120 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP3GZU		52PP3GZU		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED <sup>®</sup>	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3GRU 52PP3GSU 52PP3GTU		52PP3G2U 52PP3G3U 52PP3G9U		
	240 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP3HZU		52PP3HZU		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED $\circledast$		1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3HRU 52PP3HSU 52PP3HTU		52PP3H2U 52PP3H3U 52PP3H9U		
	480 V AC 1 3/4" (44.5 mm) mushroom head with 52AABN, 6 V 755 type lamp or option B = 52AEB*, 6 V Single LED® 600V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP3JZU		52PP3JZU		1
		red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3JRU 52PP3JSU 52PP3JTU		52PP3J2U 52PP3J3U 52PP3J9U		
		less operating head	1NO - 1NC	52PP3KZU		52PP3KZU		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED®		1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP3KRU 52PP3KSU 52PP3KTU		52PP3K2U 52PP3K3U 52PP3K9U		
	Color options	s <sup>®:</sup> blue clear white				5 A B		

Technical Specifications on page 10/169A

- (1) LED option available. For single LED only, append B to the end of the order number. Single LEDs available for all colors. LED color and lens color must match. LED option is not available on units sold "less operating head".
- Example: Single LED: 52PP3G2UB

② Blocks cannot be interchanged (start-stop circuit).

- ③ To order a color option, replace the 7th digit of the order number.
- ③ Replace asterisk (\*) in LED part number with color option that matches lens. See replacement lamps on page 10/161, for complete catalog number.

(5) Full Voltage modules are available with additional voltage ratings from the factory. For Incandescent lamps change the 6th Character to B=6V, C=12V, or E=120V (Example: Order 52PP3B2U for 6V Incandescent Lamp). For LED options change the 6th Character to B=6V AC, or E=120V AC (Example: Order 52PP3B2UB for 6V AC LED Lamp option).

10/133



### Push pull complete units

Selection and orderin	g data							_
	Version	Color of actuator	Contact blocks	Order no.	List Price	Order no.	List Price	Pack
				Plastic Head	\$	Metal Head	\$	Unit
3 Position push-pull illuminated	3 Position Push Pull, Push Maintained, Pull Momentary Illuminated, Integrated LED Module (Pull to start, push to stop) <sup>®</sup>							
	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7LRU 52PP7LSU 52PP7LTU		52PP7L2U 52PP7L3U 52PP7L9U		1
	120 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7MRU 52PP7MSU 52PP7MTU		52PP7M2U 52PP7M3U 52PP7M9U		1
	240 V AC 1 3/4" (44.5 mm) mushroom head	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7NRU 52PP7NSU 52PP7NTU		52PP7N2U 52PP7N3U 52PP7N9U		1
	3 Position Push Pull, Momentary Push Maintained, Pull Momentary Illuminated, Full Voltage (Pull to start, push to stop) <sup>®</sup>							
	24 V AC/DC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP7DZU		52PP7DZU		1
	with 52AADN, 24 V 757 type lamp or option B = 52AED*, 24 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7DRU 52PP7DSU 52PP7DTU		52PP7D2U 52PP7D3U 52PP7D9U		
	<b>3 Position Push Pull, Momentary Push</b> <b>Maintained, Pull Momentary</b> <b>Illuminated, Transformer</b> <sup>①</sup> (Pull to start, push to stop) <sup>②</sup>							
	120 V AC 1 3/4" (44.5 mm) mushroom head	less operating head		52PP7GZU		52PP7GZU		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7GRU 52PP7GSU 52PP7GTU		52PP7G2U 52PP7G3U 52PP7G9U		
	240 V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP7HZU		52PP7HZU		1
	with 52AABN, 6 V 755 type lamp or option: B = $52AEB^*$ , 6 V Single LED <sup>@</sup>	red	1NO - 1NC	52PP7HRU 52PP7HSU		52PP7H2U		
	B = OEALB , O V OINGIO ELD -	green amber	1NO - 1NC 1NO - 1NC	52PP7H50		52PP7H3U 52PP7H9U		
	480 V AC 1 3/4" (44.5 mm) mushroom head with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED <sup>®</sup>	less operating head	1NO - 1NC	52PP7JZU		52PP7JZU		1
		red	1NO - 1NC	52PP7JRU		52PP7J2U		
		green amber	1NO - 1NC 1NO - 1NC	52PP7JSU 52PP7JTU		52PP7J3U 52PP7J9U		
	600V AC 1 3/4" (44.5 mm) mushroom head	less operating head	1NO - 1NC	52PP7KZU		52PP7KZU		1
	with 52AABN, 6 V 755 type lamp or option: B = 52AEB*, 6 V Single LED®	red green amber	1NO - 1NC 1NO - 1NC 1NO - 1NC	52PP7KRU 52PP7KSU 52PP7KTU		52PP7K2U 52PP7K3U 52PP7K9U		
	Color options <sup>®</sup>					5		
clear white						A B		

**Technical Specifications** on page 10/169A

**LED option available.** For single LED only, append B to the end of the order number. Single LEDs available for all colors. LED color and lens color must match. LED option is not available on units sold "less operating head".

Example: Single LED: 52PP7JTUB

2 Blocks cannot be interchanged (start-stop circuit).

③ To order a color option, replace the 7th digit of the order number.

LED options change the 6th Character to B=6V AC, or E=120V AC (Example: Order 52PP7B2UB for 6V AC LED Lamp option).

④ Replace asterisk (\*) in LED part number with color option that matches lens. See replacement lamps on page 10/161, for complete catalog number.

⑤ Full Voltage modules are available with additional voltage ratings from the

or E=120V (Example: Order 52PP7B2U for 6V Incandescent Lamp). For

factory. For Incandescent lamps change the 6th Character to B=6V, C=12V,