

Datasheet

RS Pro Crimp Ring Terminal, M5 Stud Size, 1.5mm² to 2.5mm², 16AWG to 14AWG, Blue

RS Stock No: **613-9312**



Product Details

RS Pro crimp ring terminal in blue colour, has M5 stud size. It suits cables from 1.5 mm² to 2.5 mm² and 16 AWG to 14 AWG. A range of insulated crimp ring terminals are made from copper with flared vinyl or nylon (mini yellow) insulation. These insulated crimp ring wire connectors are colour coded for use with different wire sizes including mini yellow 0.2 - 0.5 mm² and are available with a variety of stud sizes.

Specifications:

Colour	Blue
Contact Material	Copper
Contact Plating	Tin
Inner Ring Diameter	5.3 mm
Insulation Material	Vinyl
Insulation	Insulated
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm ²)	2.5 mm ²
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm ²)	1.5 mm ²
Outer Ring Diameter	8.5 mm
Overall Length	22.8 mm
Stud Size	M5
Thickness	0.8 mm
Wire Size	16 to 14 AWG
Temperature Rating	+75°C
Amperage Rating	18 to 30 A
Voltage Rating	600 V