



Product Datasheet		Catalog Home	Home Page	Search
<h2>G1050 -- Liquidtight System</h2>				
				
Product Specifications				
Product Type	Liquidtight System			
Liquidtight System Type	Flexible Nonmetallic Liquidtight Conduit			
Trade Size	1/2"			
Color	 Gray			
Material	Co-extruded rigid and flexible PVC.			
Wet Env. Operating Temperature	0°F to +140°F (-18°C to +60°C)			
Oil Env. Operating Temperature	0°F to +158°F (-18°C to +70°C)			
Dry Env. Operating Temperature	0°F to +176°F (-18°C to +80°C)			
Flammability	New York State Office of Fire Prevention and Control. Construction Specification Institute Number 16111.			
Conduit ID/OD	.63"/.83" (16.1/21.1)			
Bend Radius	3.00" (76.2)			
Certifications	UL Listed, CSA Certified			
Voltage Rating	600V Maximum			
UPC Number	78358533363			
Weight in LBs	0.15			
Link to Drawing Library	Click here for Library			
Link to PDF Catalog	Click here for Catalog			

